

### DX 35

## Powder Actuated Fastening Tool

Semi-automatic drywall track fastening tool.

- 10 cartridges per strip in 3 power levels
- Specially designed for drywall and acoustical applications
- Pole tool available for overhead work



### Technical Data

Fastener Range	1/2" to 1-1/2"
Power Source	Hilti .25 caliber short in plastic strips of 10
Tool Weight	4.25 lb

Item No.	Description
2506	DX 35 Tool in Deluxe Kit Box Includes spare parts package, rubber stabilizer, cleaning brushes, Hilti spray lubricant, safety goggles and operating instructions in a plastic tool box

### DX E72

## Powder Actuated Fastening Tool

Single-shot, general-purpose fastening tool.

- Automatic cartridge ejection
- Padded grip for operator comfort
- Tough, durable, high-density polymer construction



### Technical Data

Fastener Range	1/2" to 2-7/8"
Power Source	Hilti .22 caliber long, single cartridge
Tool Weight	4.5 lb

Item No.	Description
1092	DX E72 Deluxe Includes spare parts package, ejection rod, rubber stabilizer, round brush, cleaning cloth, Hilti spray lubricant, safety goggles and operating instructions in a plastic tool box



## Powder-Actuated Fastening Cartridge Selection

Using Hilti powder-actuated tools combined with Hilti cartridges and fasteners produce the #1 powder-actuated fastening system in the industry! The results—the highest quality fastenings combined with safety, reliability and low maintenance.

### .22 Caliber Cartridge

For Use with:	Item No. (Qty)	Description	Power Level
DX E72	50395 (100)	5.6/16 Gray — Very Light	1 ○
	50396 (100)	5.6/16 Brown — Extra Light	2 ●
	50397 (100)	5.6/16 Green — Light	3 ●
	50398 (100)	5.6/16 Yellow — Medium	4 ●



### .25 Caliber Cartridge — (strips of 10 each)

For Use with:	Item No. (Qty)	Description	Power Level
DX 35	50106 (100)	6.3/10 M Green — Light	3 ●
	50107 (100)	6.3/10 M Yellow — Medium	4 ●
	50108 (100)	6.3/10 M Red — Heavy	5 ●
	50115 (1000)	6.3/10 M Green — Light	3 ●
	50116 (1000)	6.3/10 M Yellow — Medium	4 ●
	50117 (1000)	6.3/10 M Red — Heavy	5 ●



### .27 Caliber Cartridge — Short (strips of 10 each)

For Use with:	Item No. (Qty)	Description	Power Level
DX 351 Series	333318 (100)	6.8/11 M White — Extra Light	2* ○
DX 460 Series	50351 (100)	6.8/11 M Green — Light	3 ●
	50352 (100)	6.8/11 M Yellow — Medium	4 ●
*For DX 351 only	50353 (100)	6.8/11 M Red — Heavy	5 ●
	333317 (1000)	6.8/11 M White — Extra Light	2* ○
	50371 (1000)	6.8/11 M Green — Light	3 ●
	50372 (1000)	6.8/11 M Yellow — Medium	4 ●
	50373 (1000)	6.8/11 M Red — Heavy	5 ●



**Hilti. Outperform. Outlast.**