
SEE THE DIFFERENCE











SOLUTIONS IN A SNAP





SCAN TO VISIT OUR YOUTUBE CHANNEL

COMMITTED TO INSTALLING IN A SNAP

THE BRIDGEPORT DIFFERENCE: QUALITY, VALUE AND INNOVATION

Time and money-saving alternatives remain strong reasons to choose product from Bridgeport.

NEWDouble Snap Connectors **No Tools Required!**

New 38ADS connects metal clad and armored cable to steel boxes and enclosures. Robust, insulated throat. cULus Listed.



SNAP IN BOX



EASY, NO TOOL REMOVAL



■ New **38ACDS** snap-in connects metal clad and armored cable in old work fast. Snap the cable into the connector and then, from inside the box, snap-in the connector. Ideal for prefab construction. Robust, insulated throat. cULus Listed. Fast, Secure, Easy.



SNAP IN CABLE



SNAP IN BOX



38ADS

EASY, NO TOOL REMOVAL

Backed by Bridgeport's technical support team, strong distribution network and commitment that make us easy to do business with.



SNAP-IN "U" SHAPED STRAP DUPLEX CONNECTOR



- "U" shaped strap duplex cable retention
- Snap-in front end
- Easy removal
- cULus Listed
- Patented



Bridgeport's Complete Snap-In Fittings Line

Cable Fitting	Enclosure Opening	Cable Outer Diameter	Cable Types Listed To:	Healthcare Facility Cable	Flexible Metal Conduit	Recommended Cable Types
	KO Size	(O.D.) Range	Note: Includes Steel and Aluminum		Note: Includes Steel and Aluminum (RWFMC)	Note: Verify with cable O.D. Includes Steel and Aluminum
38ADS	1/2"	.4063	AC/MC/MCI-A	HCF	3/8" FMC/RWFMC	14/2 - 10/3
38ACDS	1/2"	.4063	AC/MC/MCI-A	HCF	3/8" FMC/RWFMC	14/2 - 10/3
3838ASP	1/2"	.3859	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/2
3838SP	1/2"	.3859	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/2
280SP*	1/2"		AC/MC/MCI-A		3/8" FMC	14/2 - 10/4
560ASP	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
560MCIA	1/2"	.3855	MC/MCI-A	HCFMCI-A		14/2 - 10/3
560SP	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
539-SS	1/2"				5/16" FMC	_
540-SS	1/2"				3/8" FMC	-
590-DC2	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
590-DCI2	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
595-DC2	1/2"	.5061	JMC/ TECK90			12/2 - 10/3
595-DC2C	1/2"	.5061	JMC/ TECK90			12/2 - 10/3
595-DCI2	1/2"	.5061	JMC/ TECK90			12/2 - 10/3
596-DC2	1/2"	.6169	JMC/ TECK90			10/4 - 8/3
596-DC2C	1/2"	.6169	JMC/ TECK90			10/4 - 8/3
596-DCI2	1/2"	.6169	JMC/ TECK90			10/4 - 8/3
616-NMD	1/2"	101 100	NM-B			14/2 - 6/2
617-NMD	3/4"		NM-B			8/2 - 6/3
620-NM	1/2"		NM-B			14/2 - 10/3
621-NM	3/4"		NM-B			8/3 - 6/3
642	1/2"	.1856	NM-B			0/0 - 0/0
643	3/4"	.2583	NM-B			
644	1 1/4"	.2598	NM-B			
645	1 1/2"	.312-1.125	NM-B			
802ASP	1/2"	.4858	AC/MC	HCF	3/8" FMC	12/2 - 10/3
802SP	1/2"	.4858	AC/MC	HCF	3/8" FMC	12/2 - 10/3
802MCIA	1/2"	.4255	MC/MCI-A	HCFMCI-A	3/0 1 1010	14/4 - 10/3
8400ASP	1/2"	.38525	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 12/3
8400SP	1/2"	.3861	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 12/3
840SP	1/2"	.4461	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
845ASP	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/6 FIVIC	14/2 - 10/3
845SP	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 10/3
84690SP	1/2"	.4261	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
	1/2"				3/8" FMC	14/4 - 10/3
846SP	1/2"	.38625	AC/MC/MCI-A	HCF/HCFMCI-A		12/2 - 10/4
850SP		.5561	AC/MC	HCF	3/8" FMC 1/2" FMC	12/2 - 10/3
851ASP 851SP	1/2" 1/2"					
		FO C1	IMC/TECKOO		1/2" FMC	10/0 10/0
895-DC2	1/2"	.5061	JMC/ TECK90			12/2 - 10/3
895-DCI2	1/2"	.5061	JMC/ TECK90			12/2 - 10/3
1701-DC**	1/2"					
1702-DC**	3/4"	4000	A O /B 4O /B 4O A	LIOE/LIOENAGE	0/0 5140	11/0 10/0
AMC-50	1/2"	.4062	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
AMC-5075	1/2"	.6292	AC/MC/MCI-A	HCF/HCFMCI-A	1/2" FMC	10/4 - 6/4
AMC-52	1/2"	.4362	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
AMC-75	3/4"	.5681	AC/MC	HCF	1/2" FMC	10/3 - 6/3
GF38SP	1/2"				3/8" FMC	
GF50SP	1/2"				1/2" FMC	
SG3838ASI		.4261	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
SG38ASP	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
SG38SP	1/2"	.4361	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
SG38MCIA	1/2"	.3856	MC/MCI-A	HCFMCI-A		14/2 - 10/3

^{*} EMT to FMC/AC/MC Combination Coupling ** EMT Quick Install Connector

MORE SNAP-IN SOLUTIONS

595-DCI2



MIGHTY-SEAL® PVC JACKETED MC AND TECK CABLE CONNECTORS

- Cable securely clamped by internal spring steel locking tabs
- Concrete and raintight
- NPT tapered threads permit threaded box installation
- Locknut and gasket for knockout installation
- Polyolefin coated versions available for direct burial
- cULus Listed
- Patented

845ASP



WHIPPER-SNAP® SNAP-IN SET SCREW CONNECTORS

- Lowest cost snap-in available
- UL Listed

Snap-in front end

- Patented
- Set screw cable retention
- Easy removal
- Low profile

3838ASP



WHIPPER-SNAP® SNAP-IN DUPLEX CONNECTORS

- Double-snap connector for duplex installation speed
- No tools required!
- Easy removal
- cULus Listed
- Patented

651SP



WHIPPER-SNAP® SINGLE SCREW STRAP CONNECTORS

- Snap-in front end
- UL Listed
- Innovative single screw strap design!
- Patented
- Easy removal
- Low profile



SG38ASP



WHIPPER-SNAP® SNAP-IN "U" SHAPED STRAP CONNECTORS

- "U" shaped strap cable retention
- Snap-in front end
- Easy removal
- cULus Listed
- Patented

AMC-50 / AMC-5075



E-Z LOCK® STEEL CONNECTORS

- Simple E-Z Lock design
- Tri-drive retention screw
- Steel construction
- cULus Listed

590-DC2



SNAP TYPE CONNECTORS

- Cable securely clamped by internal spring steel locking tabs
- Locknut front end for secure knockout installation
- cULus Listed
- Patent Pending

ALWAYS FAST.

ALWAYS EASY.

ALWAYS BRIDGEPORT.

The smarter alternative for a full line of snap-in products.

All the snap-in products you need for every installation.

Designed to work the way you work.

On the job, you'll appreciate the attention to detail and the many convenient features that make our line so easy to use.

See The Bridgeport Fittings Difference.

> It's more than a catchy name to get your attention. It's more than a marketing program to get your business. It's what makes us different. And better.

> We lower your cost by delivering quality, service, and trouble-free performance – consistently.

No surprises. No disappointments. No excuses.

ANOTHER INNOVATION FROM BRIDGEPORT US-4461 MIGHTY-HOLD® UNIVERSAL STRAPS





SUPPORTS MULTIPLE CABLE SIZES

Patented, easy to use one hole design. Also available in stainless steel for PVC Jacketed MC Cable.

US-4461 listed for use with the following:

- 14/2 10/3 STEEL AND ALUMINUM AC/MC/MCI-A
- STEEL OR ALUMINUM 3/8" FMC
- **■** cULus LISTED

THE BRIDGEPORT FITTINGS DIFFERENCE



Distributed	by:
-------------	-----



705 Lordship Blvd. Stratford, CT 06615-7313

Voice: 203.377.5944 Fax: 203.381.3488

E-mail: sales@bptfittings.com

www.bptfittings.com

CONNECTONLINE







