



“SHAKE N’ SEAL” ELECTRICAL SPLICE KITS



Kit Selector Guide

Wire Type	Butt Splice Configuration			Through Splice Configuration	
	ES137S	ES200S	ES200SV	ES200SV	ES1150
	No. of Conductors (Max.)			No. of Conductors (Max.)	
18 - 16	10	20	14	14	–
14 - 12	6	12	9	9	–
10	4	8	6	6	–
8	3	6	4	4	4
6	2	2	2	2	3
4	2	2	2	2	2
3	2	2	2	2	2
2	1	2	2	2	2
1	1	2	2	2	2
1/0					2
2/0					2
3/0					2
4/0					2
250 mcm					2
Use These Connectors Inside					

Part Number	Kit Description
ES137S	This kit has the same electrical characteristics as the ES200S but is smaller in size. It is also rated for applications up to 600v.
ES200S	This kit is perfect for parallel and branch splice applications up to 600v. Best if used with wire nut connectors.
ES200SV	This kit is perfect for small hard-to-splice areas. The clam shell-like outer closure just snaps into place over the splice. It’s versatile, and can be used for either a parallel, branch, or through splice application up to 600v with either a barrel, or wire nut type connector.
ES1150	This kit may be used with a range of cable sizes from 18 - 4/0. It is recommended for single service conductors that utilize barrel type connectors in a through splice configuration up to 5kv.

