

HEAVY DUTY TOGGLES



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 10



Fig. 11



Fig. 12

Retail Part No.	Bulk Part No.	Figure No.	Circuit Function	Poles/Throws	AMPS 125VAC	AMPS 250VAC	HP 125-250VAC	Actuator Style	Actuator Material	Bushing Length	Mounting Hole	Terminal Type	Hardware	Spec. Drawing Page No.		
35-078	35-078-BU	1	On	Off	SPST	15	10	3/4	Bat	Metal	0.465"	0.500"	Solder	N, KN	I-13 A	
35-143	35-143-BU	2	On	Off	On	4PDT	15	10	3/4	Bat	Metal	0.465"	0.500"	Screw	N, FN, Sc	I-13 B
35-145	35-145-BU	2	On	Off	Off	4PST	15	10	3/4	Bat	Metal	0.465"	0.500"	Screw	N, FN, Sc	I-13 B
35-3080	35-3080-BU	2	On	On	On	4PDT	15	10	3/4	Bat	Metal	0.465"	0.500"	Screw	N, FN, Sc	I-13 B
35-3135	35-3135-BU	3	**	10n	Off	†	15	10	1/2	Bat	Brass	0.468"	0.500"	Screw	N, FN, Sc	I-13 C
35-126	35-126-BU	4	On	Off	DPST	16	8	1	Bat	Metal	0.465"	0.500"	Screw	N, FN	I-13 D	
35-3070	35-3070-BU	4	On	Off	Off	SPST	16	8	1-1/2	Bat	Metal	0.465"	0.500"	Screw	N, Sc	I-13 E
35-139	35-139-BU	5	On	Off	Off	3PST	17	12	1-1/2	Bat	Metal	0.465"	0.500"	Screw	N, FN, Sc	I-13 F
35-140	35-140-BU	5	On	Off	On	3PDT	17	12	1-1/2	Bat	Metal	0.465"	0.500"	Screw	N, FN, Sc	I-13 F
35-141	35-141-BU	5	On	On	On	3PDT	17	12	1-1/2	Bat	Metal	0.465"	0.500"	Screw	N, FN, Sc	I-13 F
35-080	35-080-BU	6	On	Off	Off	SPST	20	10*	3/4	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc, ID	I-13 G
35-110	35-110-BU	6	On	Off	On	SPDT	20	10*	3/4	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 H
35-130	35-130-BU	6	On	On	On	SPDT	20	10*	3/4	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 H
35-144	35-144-BU	7	On	On	On	DPDT	20	10*	1-1/2	Bat	Metal	0.465"	0.500"	Solder	N, KN	I-13 I
35-146	35-146-BU	6	On	On	On	DPDT	20	10*	1-1/2	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 I
35-148	35-148-BU	6	On	Off	On	DPDT	20	10*	1-1/2	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 I
35-149	35-149-BU	7	On	Off	On	DPDT	20	10	3/4	Bat	Metal	0.465"	0.500"	Solder	N, KN	I-13 I
35-150	35-150-BU	6	(On)	Off	(On)	DPDT	20	10*	1-1/2	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 I
35-151	35-151-BU	6	On	Off	(On)	DPDT	20	10*	1-1/2	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 I
35-153	35-153-BU	8	On	Off	(On)	SPDT	20	10*	3/4	Bat	Metal	0.470"	0.500"	Screw	N, KN, Sc	I-13 H
35-155	35-155-BU	8	(On)	Off	(On)	SPDT	20	10*	3/4	Bat	Brass	0.325"	0.500"	Screw	N, KN, Sc	I-13 H
35-156	35-156-BU	7	On	On	(On)	DPDT	20	10	1-1/2	Bat	Brass	0.468"	0.500"	QC .250"	N, KN	I-13 L
35-185	35-185-BU	3	On	Off	Off	DPST	20	10*	1-1/2	Bat	Metal	0.465"	0.500"	QC .250"	N, KN	I-13 J
35-3005	35-3005-BU	9	On	Off	Off	SPST	20	10	3/4	Bat	Brass	0.325"	0.500"	QC .250"	N, KN	I-13 K
35-3010	35-3010-BU	9	On	On	On	SPDT	20	10	3/4	Bat	Brass	0.325"	0.500"	QC .250"	N, KN	I-13 K
35-3015	35-3015-BU	9	On	Off	On	SPDT	20	10	3/4	Bat	Brass	0.325"	0.500"	QC .250"	N, KN	I-13 K
35-3020	35-3020-BU	7	On	On	On	DPDT	20	10*	1-1/2	Bat	Brass	0.468"	0.500"	QC .250"	N, KN	I-13 L
35-3025	35-3025-BU	7	On	Off	On	DPDT	20	10*	1-1/2	Bat	Brass	0.468"	0.500"	QC .250"	N, KN	I-13 L
35-3045	35-3045-BU	10	On	Off	Off	DPST	20	10	3/4	Bat	Brass	0.468"	0.500"	QC .250"	N, KN	I-13 M
35-3055	35-3055-BU	9	Off	(On)	Off	SPST	20	10	3/4	Bat	Brass	0.468"	0.500"	QC .250"	N, KN	I-13 K
35-3056	35-3056-BU	9	On	Off	Off	SPST	20	10	3/4	Bat	Brass	0.325"	0.500"	Solder	N, KN	I-13 K
35-3060	35-3060-BU	3	On	Off	Off	DPST	20	10*	1-1/2	Bat	Brass	0.468"	0.500"	Screw	N, KN, Sc	I-13 N
35-3075	35-3075-BU	11	On	Off	Off	DPST	20	10	1-1/2	Bat	Brass	0.465"	0.500"	Screw	N, Sc	I-13 E
35-3170	35-3170-BU	12	On	Off	Off	SPST	***	1/2	Bat	Brass	0.500"	0.438"	Screw	KN, Sc	I-13 O	

Notes: (On)/(Off) = Momentary On/Off
 *Rated @ 277VAC
 **1&2 On
 ***Rated 35A @ 6VDC/20A @ 12VDC
 FN = Face Nut
 † = Progressive Two Circuit

ID = ID Plate
 KN = Knurled Nut
 N = Nut
 QC = Quick Connect
 Sc = Screw

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

All quantities are single; BU's are packages of 25 Unless otherwise noted.

HEAVY DUTY TOGGLES

