

SUB-MINI & MINIATURE PUSHBUTTONS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 10



Fig. 11



Fig. 12



Fig. 13

Retail Part No.	Bulk Part No.	Figure No.	Circuit Function	Poles/Throws	AMPS 125VAC	AMPS 250VAC	Bushing Length	Actuator Length	Actuator Color	Actuator Style	Terminal Type	Mounting Hole	Hardware	Spec. Drawing Page No.
35-402	35-402-BU	1	On (Off)	NC SPST	1/4*		0.125"	0.175"	Black	Pl	Sd Lug	0.172"	N	I-25 A
35-3459	35-3459-BU	2	Off (On)	NO SPST	1/4†		0.225"	0.240"	White	Pin	Sd Eyelet	0.250"	N	I-25 B
35-400	35-400-BU	3	Off (On)	NO SPST	1/2	1/4	0.125"	0.175"	Black	Pl	Sd Lug	0.172"	N	I-25 C
35-401	35-401-BU	4	Off (On)	NO SPST	1		0.276"	0.091"	Black	RC	Sd Eyelet	0.281"	N, KN	I-25 D
35-407	35-407-BU	5	Off (On)	NO SPST	1	1/2		0.100"	White	SqB	QC .187"/Sd	****		I-25 E
35-410	35-410-BU	4	Off (On)	NO SPST	1		0.276"	0.091"	Red	RC	Sd Eyelet	0.281"	N, KN	I-25 D
35-415	35-415-BU	5	Off (On)	NO SPST	1	1/2		0.100"	Red	SqB	QC .187"/Sd	****		I-25 E
35-450	35-450-BU	6	On (On)	SPDT	1*		0.250"	0.218"	White	Pin	Sd Eyelet	0.250"	2 N, LW, LR	I-25 F
35-451	35-451-BU	7	On (On)	DPDT	1*		0.250"	0.218"	White	Pin	Sd Eyelet	0.250"	2 N, LW, LR	I-25 F
35-404	35-404-BU	8	On (On)	SPDT	3		0.335"	0.315"	Black	RC	Sd Eyelet	0.250"	N, KN, W	I-25 G
35-405	35-405-BU	9	On (On)	DPDT	3		0.335"	0.315"	Black	RC	Sd Eyelet	0.250"	N, KN, W	I-25 J
35-406	35-406-BU	10	On (Off)	SPST	3		0.315"	0.315"	Black	RC	Sd Eyelet	0.315"	N, W	I-25 H
35-408	35-408-BU	10	On (On)	SPDT	3		0.315"	0.315"	Black	RC	Sd Eyelet	0.315"	N, W	I-25 H
35-409	35-409-BU	10	Off (On)	NO SPST	3		0.315"	0.315"	Black	RC	Sd Eyelet	0.315"	N, W	I-25 H
35-411	35-411-BU	11	Off (On)	NO SPST	3	1	0.295"	0.157"	Black	RB	Sd Eyelet	0.400"	N, W	I-25 I
35-412	35-412-BU	12	Off (On)	NO SPST	3	1	0.295"	0.157"	Black	SqB	Sd Eyelet	0.400"	N, W	I-25 I
35-413	35-413-BU	13	Off (On)	NO SPST	3	1	0.295"	0.157"	Black	RqB	Sd Eyelet	0.400"	N, W	I-25 I
35-417	35-417-BU	13	Off (On)	NO SPST	3	1	0.295"	0.157"	Red	RqB	Sd Eyelet	0.400"	N, W	I-25 I
35-425	35-425-BU	9	On (On)	DPDT	3		0.335"	0.315"	Blue	RC	Sd Eyelet	0.250"	N, KN, W	I-25 J

Notes: (On)/(Off) = Momentary On/Off
 *Rated@120VAC/28VDC
 ****0.500 x 0.437
 † = Rated @125VAC/DC

KN = Knurled Nut
 LR = Lock Ring
 LW = Lock Washer
 N = Nut(s)
 NC = Normally Closed
 NO = Normally Open
 N/R = Not Rated

QC = Quick Connect
 RC = Round Cap
 RqB = Rectangle Button

Pl = Plunger
 Sd = Solder
 SqB = Square Button
 W = Washer

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

All quantities are single; BU's are packages of 25 Unless otherwise noted.

SUB-MINI & MINIATURE PUSHBUTTONS (Cont.)

