

# LIGHTED APPLIANCE ROCKERS




Fig. 1



Fig. 2



Fig. 3



Fig. 4




Fig. 5




Fig. 6



Fig. 7



Fig. 8




Fig. 9



Fig. 10

## On-Off Circuit Function

Retail Part No.	Bulk Part No.	Figure No.	Poles/Throws	AMPS 125VAC	AMPS 250VAC	HP 125 VAC	HP 250 VAC	HP 125-250 VAC	Actuator Color	Actuator Material	Lamp Voltage	Mounting Hole	Spec. Drawing Page No.
35-660	35-660-BU	1	SPST	**10	N/R				Lighted Red		12V Incdt	0.550" x 1.125"	I-21 A
35-684	35-684-BU	2	SPST	12	N/R	N/R	N/R	N/R	White w/ Red LED	Plastic	***	0.430" x 1.189"	I-21 B
35-696	35-696-BU	3	SPST	15	8			1/2	Lighted Red	Nylon	125V Ne	0.508" x 0.756"	I-21 C
35-656	35-656-BU	4	SPST	15	10			1/2	Black w/Lighted Amber	Nylon	125V Ne	1.450" x 0.830"	I-21 D
35-662	35-662-BU	5	SPST	15	15	1/2	1		Lighted Amber	Nylon	12V Incdt	0.453" x 1.110"	I-21 E
35-664	35-664-BU	5	SPST	15	15	1/2	1		Lighted Green	Nylon	12V Incdt	0.453" x 1.110"	I-21 E
35-688	35-688-BU	5	SPST	15*	15	1/2	1		Lighted Red	Nylon	125V Ne	0.453" x 1.110"	I-21 E
35-689	35-689-BU	6	SPST	15	10			3/4	Lighted Red	Nylon	125V Ne	0.550" x 1.125"	I-21 F
35-3790	35-3790-BU	6	SPST	15	10			3/4	Lighted Amber	Nylon	125V Ne	0.550" x 1.125"	I-21 F
35-621	35-621-BU	7	SPST	16	16				Black w/Red Lens	Plastic	125V Ne	0.870" x 1.070"	I-21 G
35-3730	35-3730-BU	8	SPST	16	10				Lighted Amber		125V Ne	0.550" x 1.125"	I-21 H
35-3740	35-3740-BU	8	SPST	16	10				Lighted Red		125V Ne	0.550" x 1.125"	I-21 H
35-655	35-655-BU	9	DPST	20	15	N/R	N/R		Lighted Red	Plastic	125V Ne	1.000" x 1.125"	I-21 I
35-686	35-686-BU	10	DPST	20	20	1/2	1		Black w/Red Indicator	Plastic	125V Ne	1.180" x 0.870"	I-21 J
35-3750	35-3750-BU	8	SPST	20	16				Lighted Green		125V Ne	0.550" x 1.125"	I-21 H

Notes: \*Built-in Resistor  
 \*\*Rated 10 Amps @ 30VDC  
 \*\*\*Requires external resistor and diode for AC applications (not included)  
 Incdt = Incandescent  
 Ne = Neon  
 N/R = Not Rated  
 QC = Quick Connect

The Terminal Types for the above parts are QC .250" except for 35-684 is Solder and 35-696 is QC .187".

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

All quantities are single; BU's are packages of 25 Unless otherwise noted.

# LIGHTED APPLIANCE ROCKERS (Cont.)

