

## TEW Wire

For use in internal wiring of electrical and electronic equipment. Applications include electric ranges, heating equipment, lighting fixtures, panels and meters. CSA & UL Approved. For applications up to 600 Volts. Copper conductors are stranded with PVC Insulation. Temperature Rating: -40°C to 105°C (-40°F to 221°F). Available with bare copper or tin-plated copper conductors.



**B**



### TEW Wire – Bare Copper Conductors: 30m (98.4') Spools

**\*NEW**  
**\*NEW**

GA	O.D.	Stranding	Black	Blue	Brown	Green	Grey	Orange	Purple	Red	White	Yellow
18	.109"	16 x .010"	768600	768601	768602	768603	768608	768604	768599	768605	768606	768607
16	.122"	26 x .010"	768609	768610	768611	768612	768617	768613	768598	768614	768615	768616
14	.136"	41 x .010"	768618	768619	768620	768621	768626	768622	768597	768623	768624	768625
12	.159"	65 x .010"	768627	768628	768629	768630	*768635	768631	*768596	768632	768633	768634
10	.183"	105 x .010"	*768636	*768637	*768638	*768639		*768640		*768641	*768642	*768643

O.D. = Outside Diameter

**\*NEW**

### TEW Wire – Bare Copper Conductors: 300m (984') Spools

GA	O.D.	Stranding	Black	Blue	Brown	Green	Grey	Orange	Purple	Red	White	Yellow
18	.109"	16 x .010"	*768600M	*768601M	*768602M	*768603M	*768608M	*768604M	*768599M	*768605M	*768606M	*768607M
16	.122"	26 x .010"	*768609M	*768610M	*768611M	*768612M	*768617M	*768613M	*768598M	*768614M	*768615M	*768616M
14	.136"	41 x .010"	*768618M	*768619M	*768620M	*768621M	*768626M	*768622M	*768597M	*768623M	*768624M	*768625M
12	.159"	65 x .010"	*768627M	*768628M	*768629M	*768630M	*768635M	*768631M	*768596M	*768632M	*768633M	*768634M
10	.183"	105 x .010"	*768636M	*768637M	*768638M	*768639M		*768640M		*768641M	*768642M	*768643M

O.D. = Outside Diameter



### TEW Wire – Tinned Copper Conductors: 30m (98.4') Spools

GA	O.D.	Stranding	Black	Blue	Brown	Green	Grey	Orange	Purple	Red	White	Yellow
18	.109"	16 x .010"	768654	768655	768656	768657	768663	768658	768662	768659	768660	768661
16	.122"	26 x .010"	768664	768665	768666	768667	768673	768668	768672	768669	768670	768671
14	.136"	41 x .010"	768674	768675	768676	768677	768683	768678	768682	768679	768680	768681
12	.159"	65 x .010"	768684	768685	768686	768687	768693	768688	768692	768689	768690	768691
10	.183"	105 x .010"	768694	768695	768696	768697	768703	768698	768702	768699	768700	768701

O.D. = Outside Diameter

**\*NEW**

### TEW Wire – Tinned Copper Conductors: 300m (984') Spools

GA	O.D.	Stranding	Black	Blue	Brown	Green	Grey	Orange	Purple	Red	White	Yellow
18	.109"	16 x .010"	*768654M	*768655M	*768656M	*768657M	*768663M	*768658M	*768662M	*768659M	*768660M	*768661M
16	.122"	26 x .010"	*768664M	*768665M	*768666M	*768667M	*768673M	*768668M	*768672M	*768669M	*768670M	*768671M
14	.136"	41 x .010"	*768674M	*768675M	*768676M	*768677M	*768683M	*768678M	*768682M	*768679M	*768680M	*768681M
12	.159"	65 x .010"	*768684M	*768685M	*768686M	*768687M	*768693M	*768688M	*768692M	*768689M	*768690M	*768691M
10	.183"	105 x .010"	*768694M	*768695M	*768696M	*768697M	*768703M	*768698M	*768702M	*768699M	*768700M	*768701M

O.D. = Outside Diameter