

CALRAD

70 Series - Telephone Accessories

70-650

DSL SINGLE LINE MICRO FILTER

Provides uninterrupted DSL service and crystal clear conversations. Sharing a DSL connection with analog telephones may cause interference. 2 Wire DSL filters eliminate all interference between DSL line and analog telephone lines. The result is clear, clean lines for your telephones, fax machines, answering machines, caller ID and analog modems. All 2 Wire DSL filters also ensure that telephones never cause the DSL modem to adjust to the changing conditions of your DSL connection (Called retraining), which could hinder your internet access speeds. FCC approved. Male to Female RJ11. Overall length of 7". Color is off-white.



70-651

DSL LINE SPLITTER WITH SURGE PROTECTION AND DUAL MICRO FILTERS

Device splits the line to a DSL modem connectin and a analog telephone connection. Separate RJ11 female line, telephone and modem jacks. Comes with 2 mounting screws. Size: 3"L x 2.4"W x 1.09"H. Color is off-white.



70-512

INDOOR/ OUTDOOR EXTENSION TELEPHONE RINGER

An alternate to a second phone, weatherproof ABS plastic casing. Built-in modular jack for easy installation. Loud mechanical ring. Color: Ivory.



70-513

TELEPHONE LINE AND HANDSET TESTER

For testing line continuity and handset operation. Uses 9V battery (not included). Color :White.



80-566

MINIATURE TELEPHONE PICK-UP COIL

Suction cup type, attaches to phone permitting both ends of a telephone conversation to be recorded with no wiring necessary. Has 3.5mm miniature plug.



70-392 "JELLYBEAN"-STYLE TELEPHONE & ALARM INTERCONNECTS

Also known as maggots, Chiclets, beans, B-wire connectors. By using wire penetrating teeth you don't have to strip off the insulation, making it easy to splice together several wires. High-impact polycarbonate housing with thick .355mm phosphor bronze contacts. For use with 22-26 awg. wires.



- 70-392-25..... 25 Pcs.
- 70-392-100.....100 Pcs.
- 70-392-1000.....1000 Pcs.

70-392J "JELLYBEAN"-STYLE TELEPHONE & ALARM INTERCONNECTS

Gel filled type jellybean connectors also known as maggots, Chiclets, beans, B-wire connectors. By using wire penetrating teeth you don't have to strip off the insulation, making it easy to splice together several wires. High-impact polycarbonate housing with thick .355mm phosphor bronze contacts. For use with 22-26 awg. wires.



- 70-392J-25.....25 Pcs.
- 70-392J-100.....100 Pcs.
- 70-392J-1000.....1000 Pcs.

UG GEL-FILLED CONNECTOR

70-394-25.....Red, 3 port, 25 Pcs
 70-394-100.....Red,3 port, 100 Pcs
 70-394-1000...Red, 3 port, 1000 Pcs
 70-394-YL-25..Yellow ,3 port,25 Pcs
 70-394-YL-100..Yellow,3 port,100 Pcs
 70-394-YL-1000.Yellow,3 port, 1K Pcs
 70-395-25.....Yellow, 2 port, 25 Pcs
 70-395-100...Yellow, 2 port,100 Pcs
 Allows direct bridging onto existing cable conductor without service interruption. Water displacing jelly is used to minimize moisture penetration that could corrode the wiring. Available in two or three port versions. Works with 19-26 awg. wire. Packaged in 25 or 100 piece quantities.



70-393 UB GEL-FILLED CONNECTOR

Permits tapping directly into existing cable conductor without service interruption. Position and pre-crimp feature prevents conductor from slipping prior to final crimp. Water displacing jelly is used to minimize moisture penetration that could corrode the wiring. Works with 19-26 awg. wire. Packaged in 25 or 100 piece quantities.

- 70-393-25.....25 pcs
- 70-393-100..... 100 pcs.
- 70-393-1000..... 1000 pcs.

