

## Blackburn® W™ Aluminum Service Wedge Clamps

Deadend self-supporting drop wire.

Features	Benefits/Descriptions
Drop Wire May Be Cut to Exact Length	Adjustments in drop wire sag are easily made. This also saves the conductor.
Can Be Attached to Bare Neutral at Any Point in the Span	Place them where you most need them
Versatile Use	Flexible and rigid bails grip ACSR, AAC and AAAC conductors.



### Blackburn® W™ Aluminum Service Wedge Clamps

CAT. NO.	Description	Conductor Range			Dimensions (in.)		Typical Tensile Values		Colour Code
		ACSR	AL	AAAC	D	L	Conductor	Value (lb.)	
<b>W62-1</b>	W-1 Series aluminum wedge and slider	#2-#6	#1 str.-#6 sol.	#2-#6	2-3/8	12	2 (6/1) ACSR	1,200	Orange
<b>W62-1 FC</b>					flex.	17-1/2			
<b>W20-1</b>		1/0-#4	2/0 str.-#2 sol.	1/0-#4	2-3/8	12-1/2	1/0 (6/1) ACSR	1,800	Blue
<b>W20-1 FC</b>					flex.	18-1/2			
<b>W40-1*</b>		4/0-2/0	4/0 str.-2/0 sol.	4/0-2/0	2-3/8	12-3/4	4/0 (6/1) ACSR	1,900	Red
<b>W40-1 FC*</b>	flex.				18-1/2				
<b>W62-1 B†</b>	W-1B Series iridized aluminum wedge and slider	2-#6	#1 str.-#6 sol.	2-#6	2-3/8	12	2 (6/1) ACSR	1,200	Orange
<b>W62-1 BFC†</b>					flex.	17-1/2			
<b>W20-1 B†</b>		1/0-#4	2/0 str.-#2 sol.	1/0-#4	2-3/8	12-1/2	1/0 (6/1) ACSR	1,800	Blue
<b>W20-1 BFC†</b>					flex.	18-1/2			
<b>W40-1 B*†</b>		4/0-2/0	4/0 str.-2/0 sol.	4/0-2/0	2-3/8	12-3/4	4/0 (6/1) ACSR	1,900	Red
<b>W40-1 BFC*†</b>	flex.				18-1/2				

\* W40 series clamps rated 850 lb. ultimate tension for 1/0 ACSR, AL or AAAC.  
† For extremely corrosive areas.

NOTE: Catalogue numbers with "FC" suffix have a flexible bail.