





### Lampholders, Die Cast Zinc Zamak 3

	Cat. No.	Color	Lamp Max.	Description
<b>Standard</b> 	<b>L-80</b>	Silver	150W • PAR 38 or R40	Inside gasket and ground screw
	<b>D-PAK® *</b>			
	<b>DL-80</b>	Silver		
	<b>DL-80-BR</b> <b>DL-80-WH</b>	Bronze White		
<b>Gasketed</b> 	<b>L-80-D</b>	Silver	150W • PAR 38 or R40	Heavy duty slip-on gasket and ground screw
	<b>L-800</b>		150W • PAR 38 or R40	Inside gasket and ground screw
<b>Deep-Shielded</b> 	<b>L-800</b>		150W • PAR 38 or R40	Inside gasket and ground screw
	<b>LG-80</b>			Mounts to L-80 series lampholders
<b>Wireguard</b> 				Mounts to L-80 series lampholders

### Decorative Floodlight

Cat. No.	Color	Lamp Max.	Description
<b>2L80D2</b>	White	150W • PAR 38 or R40	Two lampholders round cover, inside gaskets and ground screws
<b>D-PAK® *</b>			
<b>D2L80S3</b>	Silver		

### Portable Spotlights




Cat. No.	Color	Lamp Max.	Description
<b>K702</b>	Silver	150W • PAR 38 or R40	Standard lampholder, ground spike, wall bracket, gasket, and screws
<b>K780</b>	Silver	150W • PAR 38 or R40	Deep-shielded lampholder, ground spike, wall bracket, gasket, and screws

### Compact Quartz Fixture



Cat. No.	Color	Lamp Max.	Description
<b>HV-250-CFBR</b>	Bronze	250W • Minican T4 quartz	Mighty Light® Heavy duty fixture includes mounting plate, wire nuts, and lamp

### Lampholder Covers

#### Single Gang Lampholder Covers

Cat. No.	Cat. No.	Size	Description
 LC-11	<b>Standard</b> (2 <sup>9</sup> / <sub>16</sub> " x 4 <sup>1</sup> / <sub>2</sub> ") <b>LC-11</b>		
	<b>Jumbo</b> (3 <sup>1</sup> / <sub>8</sub> " x 5 <sup>1</sup> / <sub>8</sub> ") <b>LF11</b>	1/2"	One hole Device mount
	<b>LC-21</b>	1/2"	Two hole Device mount
 LC-21	<b>LC-31</b>	1/2"	Three hole Device mount
 LC-31	<b>D-PAK® *</b>		
	<b>DLC-31</b>	Silver	1/2" Three hole Device mount
	<b>DLC-31-BR</b>	Bronze	1/2" Three hole Device mount
	<b>DLC-31-WH</b>	White	1/2" Three hole Device mount

#### Round Lampholder Covers

Cat. No.	Cat. No.	Size	Description
 S-1, SJ-11, S-12	<b>Standard</b> (4 <sup>1</sup> / <sub>8</sub> " diameter) <b>S-1-RD</b> <b>S-12</b>		
	<b>Jumbo</b> (4 <sup>1</sup> / <sub>2</sub> " diameter) <b>SJ-11</b>	1/2"	One hole
	<b>SJ-11</b>	3/4"	One hole
	<b>SJ-21</b>	1/2"	Two holes
	<b>SJ-31</b>	1/2"	Three holes
 S-3, SJ-31	<b>D-PAK® *</b>		
	<b>DSS-1</b>	Silver	1/2" One hole tapped
	<b>DSS-1-BR</b>	Bronze	1/2" One hole tapped
	<b>DSS-1-WT</b>	White	1/2" One hole tapped
	<b>DSS-3</b>	Silver	1/2" Three tapped holes
	<b>DSS-3-BR</b>	Bronze	1/2" Three tapped holes
	<b>DSS-3-WT</b>	White	1/2" Three tapped holes