

SECTION 1

Channels and Concrete Inserts

Welded Combinations

EXAMPLES
Two A1200 channels back to back are ordered as A1202. Two A1200 channels back to side are ordered as A1202C.

Back to back steel channel is riveted at every 4 inches. Aluminum back to back channel are extruded profiles. All other combinations are spot welded at every 4 inches.

End Caps and Closure Strips

<p>A804 End Cap</p>	<table border="1"> <thead> <tr> <th>Cat. No.</th> <th>For Channel</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr> <td>A804EG</td> <td>A1200</td> <td>10</td> </tr> <tr> <td></td> <td>A1400 AR1600</td> <td>10</td> </tr> <tr> <td>B804EG</td> <td>B1400 BR1600</td> <td>5</td> </tr> <tr> <td>C804EG</td> <td>C1200</td> <td>8</td> </tr> <tr> <td>E804EG</td> <td>E1200</td> <td>15</td> </tr> <tr> <td>H804</td> <td>H1200</td> <td>20</td> </tr> </tbody> </table>	Cat. No.	For Channel	Wt./C lb	A804EG	A1200	10		A1400 AR1600	10	B804EG	B1400 BR1600	5	C804EG	C1200	8	E804EG	E1200	15	H804	H1200	20	<p>Safety End Cap</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>For Channel</th> <th>Wt/C lb</th> </tr> </thead> <tbody> <tr> <td>A804NEOPWH</td> <td>A1200 AR1600</td> <td>1.75</td> </tr> <tr> <td></td> <td>A1400</td> <td></td> </tr> <tr> <td>B804NEOPWH</td> <td>B1200-BR1600</td> <td>1.5</td> </tr> <tr> <td>H804NEOPWH</td> <td>H1200</td> <td>2</td> </tr> </tbody> </table> <p>1-5/8" x 1-5/8" White Plastisol.</p>	Cat. No.	For Channel	Wt/C lb	A804NEOPWH	A1200 AR1600	1.75		A1400		B804NEOPWH	B1200-BR1600	1.5	H804NEOPWH	H1200	2
Cat. No.	For Channel	Wt./C lb																																				
A804EG	A1200	10																																				
	A1400 AR1600	10																																				
B804EG	B1400 BR1600	5																																				
C804EG	C1200	8																																				
E804EG	E1200	15																																				
H804	H1200	20																																				
Cat. No.	For Channel	Wt/C lb																																				
A804NEOPWH	A1200 AR1600	1.75																																				
	A1400																																					
B804NEOPWH	B1200-BR1600	1.5																																				
H804NEOPWH	H1200	2																																				
<p>A2431 End Cap</p> <p>For A1200 Channel Available in GoldGalv® or ElectroGalvanized (EG). Wt./C 16 lb</p>	<p>A208</p> <p>A208HDGC A208EG A208 A208SS6C</p> <p>Does not include stud nut or bolts. For A and AR series channel. Wt./C 275 lb</p>	<p>A213 Inside Joiner</p> <p>For A1200 Series only. Available only in GoldGalv® finish.</p>																																				
<p>For all channel. Standard lengths 10 ft</p>	<p>AB844PGC Pre-Galvanized Closure Strip</p> <p>AB844PCGY Plastic Closure Strip Colour: Grey</p>	<p>AB844PC Plastic Closure Strip Colour: Gold</p>																																				