



Ground Clamp



CAT. NO.	MATERIAL	WATER PIPE, COPPER TUBING SIZE	GRD. ROD SIZE
3826 [†]	M.I.	½", ¾"	½"-1"
3846 [†]	Bronze	½", ¾"	½"-1"
3849•	Brass	½"-1" O.D.	
3840-TB*	M.I.	½", ¾" or 1"	

[†]For unarmored copper wire #6, #4.

• For copper and aluminum conductors; for 14 thru 2 cu. unarmored copper wire — corrosive and outdoor use. UL approved for direct burial.

* #8 thru #4 AWG. Not CSA Certified



3849



3826

Ground Clamps for K&L Grade Copper Tubing Only



CAT.NO.	GROUND WIRE RANGE	WATER PIPE & GROUND ROD SIZE/DESC.
3844*	#8-#4	½"-1"
3888 [†]	#8-#4	½"-1" also rebar 4-10
961	#8	¾" - 1"
962**	#8	¾" - 2"
963**	#8	¾" - 3"

CAT. NO.	DESCRIPTION/CABLE SIZE
31215	Strain Relief Grounding Lug, #6 - 2
31216	Grounding Clamp, 1" Hook-Type, #6 - 2
31253	Grounding Clamp, 1-½" Hook-Type, #6 - 2
31217	Ground Clamp, 1" Straight-Type, #6 - 2
31224	Grounding Clamp, 1-½" Straight-Type, #6 - 2
31230	Wing Screw only

* With Steel Screws ** With Bronze Screws, Not CSA Certified — or UL Listed

[†]UL approved for direct burial. Silicon Bronze Screws.



961

For radio, motor frame and equipment grounding



3840-TB



31215

Disconnect static ground clamp and lug, straight-type (cable not supplied), UL not applicable



3844

For armored and unarmored wire

Cable Tray Ground Clamp



Material: Malleable iron

Standard Finish: Zinc plated



CAT. NO.	DESCRIPTION
10105*	For Single Conductors #4 sol. to 2/0 str.
10109**	For Single Conductors 2/0 sol. to 4/0 str.

* UL Listed #4 to 2/0 AWG copper

** UL Listed 2/0 to 4/0 AWG copper/aluminum

CSA File No. 2884