

EZL500 Thermal Label Printer



EZL500 Thermal Label Printer

| Cat. Number | Description | UPC Number |
|-------------------|---|--------------|
| EZL500 | Handheld Thermal Label Printer (includes EZL500 Thermal Label Printer, EZ-1030C-WN label cassette, six AA batteries, quick-start guide and user's manual) | 782609-91656 |
| EZL500-KIT | Handheld Thermal Label Printer Kit with Accessories (includes EZL500 Thermal Label Printer, EZ-1030C-MP and EZ-1030C-WN label cassettes, PA-EZL500 power adapter, MS-EZL500 magnet strap, PCS-EZL500 PC software and USB cable, RB-EZL500 rechargeable battery, quick-start guide, user's manual and CC-EZL500 carrying case) | 782609-91657 |



EZL500 Accessories

| Cat. Number | Description | UPC Number |
|-------------------|--------------------------------------|--------------|
| PA-EZL500 | EZL500 Power Adapter | 786209-91682 |
| MS-EZL500 | Magnet Strap for EZL500 | 786209-91683 |
| PCS-EZL500 | PC Software and USB Cable for EZL500 | 786209-91685 |
| CC-EZL500 | Hard Carrying Case for EZL500 | 786209-91686 |
| RB-EZL500 | EZL500 Rechargeable Battery | 786209-92262 |

EZL500 Thermal Label Printer Tapes

- **Nylon** — Excellent for wire and cable wrapping on curved, textured and highly textured surfaces, these flexible labels feature EZ-Peel split backs and industrial-strength adhesive
- **Polyester** — Perfect for general labeling on flat or textured surfaces, these labels also come with EZ-Peel split backs and industrial-strength adhesive
- **Heat-Shrink** — Made of flame-retardant polyolefin with 3:1 shrink ratio for extra protection and insulation of wire and cable, these labels meet MIL-DTL-23053/5 classes 1 and 3 standards
- **Vinyl** — Able to resist oil, dirt, grime and solvents on smooth, textured or curved surfaces, this flexible label features an EZ-Peel split back and industrial-strength adhesive; it's excellent for indoor/outdoor use



EZ-1230C-WN



EZ-3430C-WP

EZL500 Label Printer Tapes

| Cat. Number | Material | Color | Width | UPC Number |
|---------------------|-----------------------|-------------|-------|--------------|
| EZ-3830C-WN | Nylon | White | 3/8" | 786209-91658 |
| EZ-1230C-WN | Nylon | White | 1/2" | 786209-91659 |
| EZ-3430C-WN | Nylon | White | 3/4" | 786209-91660 |
| EZ-1030C-WN | Nylon | White | 1" | 786209-91661 |
| EZ-3830C-YN | Nylon | Yellow | 3/8" | 786209-91662 |
| EZ-1230C-YN | Nylon | Yellow | 1/2" | 786209-91663 |
| EZ-3430C-YN | Nylon | Yellow | 3/4" | 786209-91664 |
| EZ-1030C-YN | Nylon | Yellow | 1" | 786209-91665 |
| EZ-3830C-WP | Polyester | White | 3/8" | 786209-91666 |
| EZ-1230C-WP | Polyester | White | 1/2" | 786209-91667 |
| EZ-3430C-WP | Polyester | White | 3/4" | 786209-91668 |
| EZ-1030C-WP | Polyester | White | 1" | 786209-91670 |
| EZ-3830C-MP | Polyester | Metallic | 3/8" | 786209-91671 |
| EZ-1230C-MP | Polyester | Metallic | 1/2" | 786209-91672 |
| EZ-3430C-MP | Polyester | Metallic | 3/4" | 786209-91673 |
| EZ-1030C-MP | Polyester | Metallic | 1" | 786209-91674 |
| EZ-1412C-WHS | Heat-Shrink | White | 1/4" | 786209-91675 |
| EZ-3812C-WHS | Heat-Shrink | White | 3/8" | 786209-91676 |
| EZ-1212C-WHS | Heat-Shrink | White | 1/2" | 786209-91677 |
| EZ-1412C-YHS | Heat-Shrink | Yellow | 1/4" | 786209-91678 |
| EZ-3812C-YHS | Heat-Shrink | Yellow | 3/8" | 786209-91679 |
| EZ-1212C-YHS | Heat-Shrink | Yellow | 1/2" | 786209-91680 |
| EZ-1030C-SL | Self-Laminating Vinyl | White/Clear | 1" | 786209-91681 |

www.tnb.com

Thomas & Betts

Please ask your Thomas & Betts sales representative for a complete catalog of quality Thomas & Betts electrical products or visit us at www.tnb.com. For customer service, call 1-800-816-7809. For technical questions, call 1-888-862-3289.

Thomas & Betts Corporation
Electrical Division
8155 T&B Boulevard
Memphis, TN 38125
901-252-5000

Thomas & Betts Ltd.
700 Thomas Avenue
Iberville, Québec J2X 2M9
450-347-5318