

Fitting Number Selection

SHF624LV09024

Fitting Material	Siderail Depth	Width	Bottom Type	Fitting Type	** Angle	† Nominal Radius
SPF • Pre-Galvanized Fittings SHF • Hot Dip Galvanized Fittings SSF • Stainless Steel 316	3 • (3-5/8") 4 • (4") 5 • (5") 6 • (6") 7 • (7")	06 • (6") 09 • (9") 12 • (12") 18 • (18") 24 • (24") 30 • (30") 36 • (36")	* L • Ladder *** V • Ventilated ***** S • Solid Trough	HB • Horizontal Bend HT • Horizontal Tee HX • Horizontal Cross VI • Vertical Inside Bend VO • Vertical Outside Bend VTD • Vertical Tee Down VTU • Vertical Tee Up HYR • Horizontal Wye Right HYL • Horizontal Wye Left RT • Horizontal Reducing Tee ET • Horizontal Expanding Tee EX • Horiz. Expand Cross HLR • Horizontal Left Reducer HSR • Horizontal Straight Reducer HRR • Horizontal Right Reducer CS • Cable Support Fitting	30 • (30°) 45 • (45°) 60 • (60°) 90 • (90°)	12 • (12") 24 • (24") 36 • (36") 48 • (48")

** Angle is required for HB, VI, VO only.

† Radius is not required for the following Fitting Types: **HYR, HYL, HLR, HRR, HSR**

* Manufactured with 9" rung spacing measured at the center line of fitting.

*** Manufactured with 4" edge to edge rung spacing measured at the center line of fitting.

***** Manufactured with flat sheet inserted under rungs with 9" rung spacing measured at the center line of fitting.