

GFCIs & POWER PRODUCTS

INDOOR



NOTE: Approvals are CSA and UL for all products on this page unless otherwise noted.



14650W & 14650Y SINGLE OUTLET GFCI PLUG ADAPTER

Provides GFCI and surge protection for tools used indoors. Available in white (14650W) and yellow (14650Y with booted buttons).

- + RESET: Manual
- + VOLTS/AMPS: 120V/15A
- + TRIP LEVEL: 4-6mA



33120 & 33240 INDOOR PANEL MOUNT GFCI-AUTO RESET

Provides GFCI protection for personnel and equipment, these panel mounts are ideal for OEM applications that require a mounted unit. Wire leads coming out of the unit allow for easy installation.

33120

- + RESET: Automatic
- + VOLTS/AMPS: 120V/20A
- + TRIP LEVEL: 4-6mA

33240

- + RESET: Automatic
- + VOLTS/AMPS: 240V/20A
- + TRIP LEVEL: 4-6mA



24220 & 41240 INDOOR PANEL MOUNT GFCI-MANUAL RESET

Provides protection for personnel and equipment, these panel mounts are ideal for OEM applications that require a mounted unit. Quick disconnect terminals makes set-up simple.

24220

- + RESET: Manual
- + VOLTS/AMPS: 120V/20A **OR** 240V/16A
- + TRIP LEVEL: 10mA

41240

- + RESET: Manual
- + VOLTS/AMPS: 120V/15A
- + TRIP LEVEL: 4-6mA



14880PS-903 GFCI & CIRCUIT BREAKER POWER BAR

A six-outlet power bar complete with GFCI plug and breaker. A three foot 14/3 cord brings safe power distribution to where you need it. On/Off switch on the power bar.

- + RESET: Manual
- + VOLTS/AMPS: 120V/15A
- + TRIP LEVEL: 4-6mA