

INDOOR/OUTDOOR

These portable GFCIs are durable enough to be used both indoors and outdoors on the toughest work environments. Rainproof rated and listed for outdoor use, these are the units you need for ground-fault protection on the job site.



NOTE: Approvals are CSA and UL for all products on this page unless otherwise noted.

GFCI PLUG & CORD SETS

14880 SERIES GFCI PLUG AND CORD SET

GFCI plug and cord set that plugs into an outlet and provides between 9" and 50' of cord with female receptacle end.

ALL ITEMS ARE:

- + RESET: Manual
- + TRIP LEVEL: 4-6mA
- + VOLTS/AMPS: 120V/15A
- + CORD TYPE: SJTW yellow cord



PART NO.	CORD LENGTH & TYPE
14880-4001	9" 14/3 cord
14880-4006	6' 14/3 cord
14880-4025	25' 14/3 cord
14880-4050	50' 14/3 cord

PART NO.	CORD LENGTH & TYPE
14880-2001	9" 12/3 cord
14880-2006	6' 12/3 cord
14880-2025	25' 12/3 cord
14880-2050	50' 12/3 cord

INLINE GFCI CORD SETS

26020L SERIES INLINE GFCI PLUG CORD SET

Inline GFCI cord set for providing rugged, portable GFCI protection to cord sets and equipment. Great for industrial plant maintenance, equipment service and construction site applications. Indicator light on unit displays when there is power on.

ALL ITEMS ARE:

- + RESET: Manual
- + TRIP LEVEL: 4-6mA
- + VOLTS/AMPS: 120V/15A
- + CORD TYPE: SJTW yellow cord



PART NO.	CORD LENGTH & TYPE
26020L-4001	14" 14/3 cord
26020L-4006	6' 14/3 cord
26020L-4025	25' 14/3 cord
26020L-4050	50' 14/3 cord
26020L-4002L	2' 14/3 cord, twist-lock connectors

PART NO.	CORD LENGTH & TYPE
26020L-2001	14" 12/3 cord
26020L-2006	6' 12/3 cord
26020L-2025	25' 12/3 cord
26020L-2050	50' 12/3 cord