

INDUSTRIAL LIGHTING

HAND LAMPS & WORK LIGHTS

INCANDESCENT/CFL HEAVY-DUTY

LE100 HEAVY-DUTY RUBBER WORK LIGHT

This model has an extremely rugged design for long life in abusive industrial conditions. The one-piece molded construction tightly seals against the cord and socket to prevent the entry of moisture and dirt. Convenient swivel hook and smooth reflector featured on the guard.

APPROVALS: CSA and UL Certified



BULB RATING: Up to a 100W 120V A-21 incandescent or CFL bulb (not included)

LIGHT OUTPUT: Dependent upon bulb

LENGTH: 16.5"

DIAMETER: 4.1"

CONSTRUCTION: High-visibility yellow rubber handle resists grease, oils, solvents, and extreme temperatures. Guard is made of extra-heavy gauge steel wire and is zinc coated to resist corrosion.

Meets OSHA requirements No. 1926.403(g) and No. 1926.405(j) (iii).

FEATURES: Heavy-duty neoprene 16/3 SOW cable which is oil/weather resistant, and stays flexible in cold temperatures.

LE100-25P with 25' cord and plug, 4.3 lbs

LE100-50P with 50' cord and plug, 6.5 lbs

LE100-100P with 100' cord and plug, 11.4 lbs



LE103 HEAVY-DUTY HAND LAMP

With a durable oversized metal guard and a grounded convenience outlet in the handle, the LE103 provides you the flexibility of bringing extra power with you to your task. The outlet has a 15A circuit breaker to protect against power overloads, which can cause electrical fires. Includes an on/off switch in the handle.

APPROVALS: cULus Certified



BULB RATING: Up to a 100W 120V incandescent or CFL bulb (not included)

LIGHT OUTPUT: Dependent upon bulb

LENGTH: 17"

DIAMETER: 4.3"

CONSTRUCTION: Molded plastic handle. Swing-open guard with reflector allows tool-free bulb replacement.

FEATURES: Weather resistant 14/3 SJTW cord comes in high-visibility yellow, and allows for increased current carrying capacity.

LE103-25P with 25' cord and plug, 3.9 lbs

LE103-50P with 50' cord and plug, 6.1 lbs

