

INDUSTRIAL LIGHTING

HAND LAMPS & WORK LIGHTS

LED INDUSTRIAL

LED6015 LED WORK LIGHT

The LED6015 has 55 LEDs, providing greater light output across its longer dimensions without dramatically increasing weight.

APPROVAL: cULus Certified



BULB: 55 LED, 3.95W
LIGHT OUTPUT: 133 lumens
LENGTH: 18.5"
WIDTH: 2"
HEIGHT: 1.5"
WEIGHT: 2.1 lbs
CONSTRUCTION: Molded plastic housing



LED6015 15' 18/2 SJT cord

LED5015G LED WORK LIGHT

Packing 50 LEDs into a compact space, the LED5015G is bright white light where you need it most. It incorporates a 13A convenience outlet in the handle so that you can plug in additional tools. The LED5015G also comes with a removable magnet mount and dual hooks so that it can be positioned exactly where you need it.

APPROVAL: cETLus Certified



BULB: 50 LED, 3.39W
LIGHT OUTPUT: 112 lumens
LENGTH: 15"
WIDTH: 3.5"
HEIGHT: 2"
WEIGHT: 2.9 lbs
CONSTRUCTION: Molded plastic housing



LED5015G 15' 16/3 SJT cord



Put lights LE1425LED/LED6015/LED5015G on a reel. See page 44.