

# INDUSTRIAL LIGHTING

## BATTERY POWERED

### LANTERNS & SPOTLIGHTS HEAVY-DUTY

#### LE945 RECHARGEABLE LANTERN

These cordless rechargeable lanterns deliver long lasting performance in a durable package. This light offers several unique features including:



- + Quality GE Sealed beam halogen bulb or bright LED array
- + Rechargeable 6V gel cell battery
- + Built-in over-charge protection
- + Includes adjustable stand
- + Optional magnet mount and nylon shoulder strap available

#### HALOGEN BULB OFFERS:

- + 4-5 hours of constant operation
- + 8-10 hours of intermittent operation

#### LED BULB OFFERS:

- + 25+ hours of constant operation
- + SPOT MODE: 3W, 110 lumens
- + FLOOD MODE: 0.17W, 56 lumens



The LE945 also offers three mountable charging bracket options for use in a variety of applications.

- + 120V AC plug-in charger for wall outlets
- + 12V DC plug-in charger for auto receptacles
- + 12V DC hardwire charger with inline fuse for permanent vehicle mounting



We also have an Emergency-On Lantern, the LE946. Same outstanding features as the LE945 plus automatically turns on if there is a power failure. See below.

PART NO.	CHARGER TYPE	BULB TYPE
LE945-1YS	120V AC Charger	8W spot
LE945-1YF	120V AC Charger	8W flood
LE945-1LED	120V AC Charger	LED array
LE945-2YS	12V DC Plug-In Charger	8W spot
LE945-2YF	12V DC Plug-In Charger	8W flood
LE945-2LED	12V DC Plug-In Charger	LED array
LE945-3YS	12V DC Hardwire Charger	8W spot
LE945-3YF	12V DC Hardwire Charger	8W flood
LE945-3LED	12V DC Hardwire Charger	LED array
LE946-1YS	120V AC Charger	8W spot
LE946-1YF	120V AC Charger	8W flood
LE946-1LED	120V AC Charger	LED array

REPLACEMENT BULB: Spotlight - P/N **H7550** • Floodlight - P/N **H7551**

REPLACEMENT BATTERY: P/N **6V4P**

## LANTERNS & SPOTLIGHTS HEAVY-DUTY

### 2150 SERIES PATROL LIGHT

This rugged emergency patrol and utility light offers excellent light output combined with a nearly indestructible neoprene construction. This product features a sealed beam bulb that penetrates through glass, smoke, and fog. It also offers a pistol grip with activation trigger for single handed operation, and a handle ring for hanging storage. This model comes complete with a heavy duty 12' 18/2 coil cord and a cigarette lighter plug.

**2150-509** 50W Halogen bulb

**REPLACEMENT BULB:** P/N **2150-95**



## LANTERNS & SPOTLIGHTS INDUSTRIAL

### 2,000,000 CANDLEPOWER SPOTLIGHTS

- + Quartz halogen beam technology for maximizing beam power and distance
- + Durable black ABS housing and non-skid rubber bezel
- + 12V, 2.8 amp battery/100W quartz halogen bulb

**QR-2002** Features an internal, memory-free rechargeable battery with 15-20 minutes constant operating time (30-40 minutes intermittent use) on a full charge. Comes with 110V and 12V charging cords, and a 12V cord for continual powered operation.

**REPLACEMENT BATTERY:** P/N **QR-12VB**

**QH-2002** Operates from any standard 12V cigarette lighter receptacle

**REPLACEMENT BULB FOR BOTH SPOTLIGHTS:** P/N **01-0430-01**

