

INCANDESCENT/CFL INDUSTRIAL

LE104 INDUSTRIAL ALL-TEMPERATURE WORK LIGHT

Our LE104 all-temperature light is designed to keep working in the temperature extremes that you face. The 16/3 SJTOW cord stays flexible in cold temperatures and resists high temperatures. It also has a convenience outlet with 13A circuit breaker to let you bring additional power to your task. Includes an on/off switch in the handle.

APPROVAL: cULus Certified

BULB RATING: Up to a 100W 120V incandescent or CFL bulb (not included)

LIGHT OUTPUT: Dependent upon bulb

LENGTH: 14.6"

DIAMETER: 3.5"

CONSTRUCTION: Molded plastic handle. Swing-open guard with reflector allows tool-free bulb replacement.



LE104-25P with 25' cord and plug, 2.5 lbs

LE104-50P with 50' cord and plug, 4.1 lbs

LE105 GENERAL PURPOSE HAND LAMP

The LE105 is an affordable hand lamp for those applications that do not require specialized capabilities. It has a grounded 13A convenience outlet and on/off switch in handle.

APPROVAL: cULus Certified

BULB RATING: Up to a 100W 120V incandescent or CFL bulb (not included)

LIGHT OUTPUT: Dependent upon bulb

LENGTH: 12.6"

DIAMETER: 3.5"

CONSTRUCTION: Molded plastic handle. Swing-open guard with reflector allows tool-free bulb replacement. 16/3 SJT cord.



LE105-25P with 25' cord and plug, 2.5 lbs

LE105-50P with 50' cord and plug, 4.2 lbs