FLUORESCENT HEAVY-DUTY

LE5025 LUMENEXTM FLUORESCENT WORK LIGHT

This rugged 50W light is for when you need portable illumination of a larger work area. It features the same polycarbonate shield and virtually indestructable construction of our other LumenexTM lights, but with the largest bulb yet. Comes with hanging hook, handle and on/off switch on cord.

APPROVAL: cETLus Certified

LIGHT OUTPUT: 4,300 lumens

LENGTH: 30"
DIAMETER: 3.75"
WEIGHT: 7 lbs

CONSTRUCTION: Polycarbonate outer tube,

rubber end caps and handle

LE5025 with 25' of 16/3 SJEOW cold-weather rated cord and plug

REPLACEMENT BULB: P/N PLL50/CW/RS





FLUORESCENT INDUSTRIAL

UPL25G AND UPL50G FLUORESCENT HAND LIGHT

Our 13W UPL lights are industrial quality fluorescent hand lamps with a 13A convenience outlet at the base of the light for plugging in power tools. The UPL has a shatter resistant polycarbonate lamp shield to stand up to abuse. It includes a full-length reflector, switch, hook, and removable magnet mount.

APPROVAL: cULus Certified

BULB: 13W twin-tube compact fluorescent

LIGHT OUTPUT: 900 lumens

LENGTH: 13" DIAMETER: 2.75" WEIGHT: 4 lbs

CONSTRUCTION: Polycarbonate outer tube,

molded plastic handle

UPL-25G 25' 16/3 SJTW cord

UPL-50G 50' 16/3 SJTW cord

REPLACEMENT BULB: P/N PL13/CWRS

USABLE LIGHT

SCALE

SCALE

PAGE 16 FOR PERF



Put the UPL on a cable reel. See page 44.