

## Heavy Duty LED Work Lights LIGHTWEIGHT • VIRTUALLY INDESTRUCTIBLE

Our incredibly popular line of heavy-duty work lights now has two new LED models. The LE1725LED and LE1625LED work lights are quickly becoming the favourite choice for customers across the country. The polycarbonate lens and rubber handle make these models virtually indestructible. With features such as having no bulbs to replace, a lightweight rugged design, dual steel rotatable hanging hooks and the latest in LED technology, the LE1725LED and LE1625LED are very high-value work lights.



The LE1725LED has the same usable light output as a 13W fluorescent work light but with superior LED technology to operate as a worklight and as a flashlight due to the extra LED in the top end.



The **LE1625LED** is the value priced choice. It has the same durability as our other heavy duty LED work lights but at a lower price point with less light output.

	LE1725LED	LE1625LED
BULB	2 x 4W high output white LEDs. Extra LED in top end for flashlight function	1 x 4W high output white LED
LIGHT OUTPUT	480 Lumens	240 Lumens
LENGTH	11.5"	8.0"
DIAMETER	2.25"	2.25"
WEIGHT	1.0 lb light head only	
CONSTRUCTION	Replaceable polycarbonate lens, rubber end cap, Nylon 66 hard plastic, chemical resistant handle. Switch in handle. Dual steel hanging hooks.	
CABLE	25' 18/2 SJTOW, Black	25' 18/2 SJTOW, Yellow
PART NUMBER TO ORDER ON 40' REEL	LE1740RLED	LE1640RLED



For more information about our other lines of portable electrical equipment for the toughest workplaces: www.lindequipment.net | info@lindequipment.net | T: 877.475.LIND