

THE BEACON LIGHT - 30W & 50W


KEY FEATURES

- As bright as a 500W quartz halogen (50W version).
- Low energy usage (only 30W or 50W).
- No bulb replacement required.
- AC & DC voltages available.
- IP65 weatherproof rated.
- Instant start-up, at full output, even in cold temperatures.
- Cool to the touch, even if left running for extended lengths of time.
- Durable cast aluminum housing.

KEY BENEFITS

- Safer working environment.
- Lower total cost of ownership.
- Reduced downtime on job sites.
- Energy saving device for a greener footprint.
- Extremely versatile light for multiple applications.

The Beacon Light is the only portable LED floodlight on the market that is built strong enough to withstand the toughest environments without compromising on high-quality light output. The Beacon Light projects a wide, shadow-free flood of crisp bright white light generated via a 30W or 50W LED integrated chip, which is solid-state and can therefore endure shocks, vibrations and rough handling without breaking the LEDs. The Beacon will provide an instant start in even the coldest locations, and the unit remains cool-to-the-touch even if left running for days.



LE970LED-TR
Tripod model



LE970LED-TD
Dual-head tripod model



LE965LED-FS-DC
Floor stand model



LE970LED-MAG-DC
Magnet mount model



LE965LED-CLAMP
Clamp mount model

INDUSTRIES

- Construction
- General industry
- Mining
- Utilities
- Fabrication workshops
- Tank manufacturing/maintenance



Scan for more info

SPECIFICATIONS

SPECIFICATIONS	
BULB TYPE AND RATING	High output integrated LED array. Rated for over 50,000 hours.
LIGHT OUTPUT	50W: 5,000 Lumens • 30W: 3,000 Lumens
VOLTAGE RATING OPTIONS	50W: 120V AC or 24V DC 30W: 120V AC or 12V DC
LIGHT TEMPERATURE	4500K (bright white light - no blue tint)
CONSTRUCTION	Cast aluminum housing with powder-coat yellow paint
ENVIRONMENTAL RATING	IP65 Weatherproof
WEIGHT (light head only)	50W: 10 lbs. • 30W: 8 lbs.
CORD TYPE	15' 18/3 SJTOW, black
APPROVALS	cETLus

