








RETRACTABLE ASSEMBLIES

Eliminate tangled bonding and grounding assemblies that lie on the floor and present a tripping hazard. Coiled assemblies neatly and compactly retract out of the way when not in use. The coiled plated steel cable is bright orange PVC coated for high visibility.

PART NO.	LENGTH	SIZE	O.D.	TERMINATION 1	TERMINATION 2	
	RAC-5	5'	1/8"	3/16"	REB hand clamp	5/16" lug terminal
	RAC-10	10'	1/8"	3/16"	REB hand clamp	5/16" lug terminal
	RAC-15	15'	1/8"	3/16"	REB hand clamp	5/16" lug terminal
	RAC-10+10	20'	1/8"	3/16"	REB hand clamp	5/16" lug terminal
	RAC-30	30'	1/8"	3/16"	REB hand clamp	5/16" lug terminal
	RAC-20	20'	3/16"	1/4"	GAT-P large aluminum hand clamp	3/8" lug terminal
	RAC-20B	20'	3/16"	1/4"	GAT-PCU large bronze hand clamp	3/8" lug terminal

NOTE: RAC assemblies can also have REB or other clamps on both ends. Ask us for assistance.

ASSEMBLIES INDUSTRIAL

PART NO.	CABLE	TERMINATION 1	TERMINATION 2
LE62	 3' of 1/8" plated steel cable	LE-25C alligator clip, opens 3/4"	LE-25C alligator clip, opens 3/4"
LE63	 3' of 1/8" plated steel cable	LE-25C alligator clip, opens 3/4"	5/16" copper lug terminal
LE64	 3' of 1/8" plated steel cable	LE-25C alligator clip, opens 3/4"	EP-1, 3/4" C-clamp
LE70	 3' of 1/8" plated steel cable	5/16" copper lug terminal	5/16" copper lug terminal
LE72	 3' of 3/32" PVC coated cable	LE-25C alligator clip, opens 3/4"	LE-25C alligator clip, opens 3/4"
LE79	 3' of 3/32" PVC coated cable	LE-25C alligator clip, opens 3/4"	EP-1, 3/4" C-clamp

For any assembly that comes with a standard 3' length, add **-72** to the part number to change the length to a 6' cable, or **-120** for 10' cable. Please contact one of our sales representatives for assistance with other custom lengths.

BONDING & GROUNDING FACT

A higher velocity of liquid transfer = a higher rate of static charge generation. Slow it down!