

Code•Master™ Jr. LED Factory Sealed Luminaires

Explosionproof, Dust-Ignitionproof

For use with threaded metal conduit.


NEC/CEC:

Class I, Division 1, Groups B, C, D ①
 Class II, Division 1, Groups E, F, G
 Class III
 Zone 1, Ex db IIB + H₂
 NEMA 3R, 4X





NEC/CEC:

Suitable for use in Wet Locations
 Marine Outside Type (Salt Water)

Fixture Housing (Not including mounting hoods)

	Description	Weight kg (lb)	Catalog Number
	1600 Lumens, 5000K, 120-277 Vac and 100-300 Vdc	5.2 (11.5)	CJLL1CBU
	3000 Lumens, 5000K, 120-277 Vac and 125-300 Vdc	5.2 (11.5)	CJLL2CBU
	5150 Lumens, 5000K, 120-277 Vac and 100-300 Vdc	5.5 (12.0)	CJLL3CBU
	5150 Lumens, 5000K, 120-277 Vac and 100-300 Vdc	5.5 (12.0)	CJLL3CBH
	1500 Lumens, 3000K, 120-277 Vac and 125-300 Vdc	5.2 (11.5)	CJLL1WBU
	2900 Lumens, 3000K, 120-277 Vac and 100-300 Vdc	5.2 (11.5)	CJLL2WBU
	5100 Lumens, 3000K, 120-277 Vac and 125-300 Vdc	5.5 (12.0)	CJLL3WBU
	5100 Lumens, 3000K, 120-277 Vac and 125-300 Vdc	5.5 (12.0)	CJLL3WBH

Mounting Hoods

	Type Mounting	Hub Size (Inches)	Certified for Class I, Division 1 and 2, Groups	Hood Weight kg (lb)	Catalog Number
Pendant					
	One Hub Rigid Conduit	3/4	C, D	0.9 (1.98)	CAP-75
			B, C, D		CAP-75B
		1	C, D	0.9 (1.98)	CAP-100
			B, C, D		CAP-100B
Ceiling					
	Four Hubs Three Close-Up Plugs Rigid Conduit	3/4	C, D	1.8 (3.97)	CAC-75
			B, C, D		CAC-75B
		1	C, D	1.8 (3.97)	CAC-100
			B, C, D		CAC-100B
Bracket					
	Four Hubs Three Close-Up Plugs Rigid Conduit	3/4	C, D	2.7 (5.95)	CALB-75
			B, C, D		CALB-75B
		1	C, D	2.7 (5.95)	CALB-100
			B, C, D		CALB-100B
25° Stanchion					
	One Hub	1-1/4 or 1-1/2	C, D	0.9 (1.98)	CAS-150 ②
			B, C, D		CAS-150B

① For Group B applications, a Group B rated mounting hood must be used.

② 1-1/2" Tapped hub furnished with 1-1/2" to 1-1/4" reducer.