

FANS

Fan Controls and Accessories



CQ002

Fan remote control, c/w canopy type receiver, 4 speeds including off, light on/off or dimmer, fits most all brands that are canopy remote control adaptable.



CQ003

Ceiling fan wall mount light & fan control, 4 speeds including off, 5 levels of brightness & off, operates only on 3 wire (14/3 etc)



CQ004

Controls ceiling fan from wall control. Four speeds including off. Cannot wire lights through this control.



CQ005

Fan remote control, c/w canopy type receiver, 4 speeds including off, light on/off or dimmer, manual temperature setting, timer for fan and/or light, light delay.



WS203WH White

Wall mount ceiling fan and light control, 3 speed slide fan control, high, med, low, off light control, c/w wall plate not shown



MC3 Runs up to 2 fans

MC5 Runs up to 4 fans

MC10 Runs up to 8 fans

MC15 Runs up to 12 fans

FR5 up to 4 fans, fwd/rvs, surf. mount

FRMC5 up to 4 fans, fwd/rvs, box mount Industrial Fan Speed Controls. Features infinite speed adjustment, minimum speed adjustment screw. All controls are designed to fit a 3" x 5" electrical box. (Except FR5 which is surface mount)



RC-5000

Wall Mount Fan remote control, c/w canopy type receiver, 3 speeds, full range dimmer, last setting memory, fits most all brands that are canopy remote control adaptable, operates on 2 wire system



SEE OUR ELECTRICAL SECTION FOR EVEN MORE CHOICES ON FAN & LIGHT CONTROLS

All Your Fan

Accessory Needs:

- Blades
- Blade Brackets
- Balancing Kits
- Mounting Brackets
- Capacitors
- Switch Housing Covers
- Switches
- Special Downrods
- Upper Canopy
- Light Kit Cap-offs and more.....



RLTSW002

2-Way Light

CQ6000800

3-Way Light

RSPB

3-Wire Fan Speed

RRVI

Fwd / Rvs Switch

Fan/Light switch, 3/8" threaded end, universal, pull chain style

CQ0023240

24" Ceiling fan chain, comes with 3 connectors. Polished brass finish.



FC03

Fan function tassels. Polished brass finish.