



CP - COMMERCIAL CEILING FANS

MODEL: CP56 F&R

ENERGY SAVINGS • COST EFFECTIVE • EFFICIENT





Features

- Ideally suited for circulating air in Industrial and Commercial Applications.
- Canarm's "CP" Fans help save energy year round.
- 56" blade sweep
- Variable speed motor (all motors are impedance protected, PSC type variable speed with permanently lubricated ball bearing motors).
- When used with our MC series speed controls the speed range is infinite.
- Painted steel blades with curved ends deliver maximum airflow over wide areas.
- Reversible motor provides both winter destratification and summer time cooling.

Performance Data & Specifications

Model Number	Color	Airflow	Fan Size	Max RPM	Air Velocity 5' from fan	Air Delivery @ floor	Amps High	Watts High	Downrod Length	Shipping Weight (Lbs.)
CP56 F&R	White	Up/Downdraft	56"	310	660 ft/min	20,500 cfm	0.90	97	16"	17.00



CEILING FAN SPEED CONTROLS

MODELS: "MC" CONTROL & "FRMC5" CONTROL

"MC" CONTROL

- Available in 4 models: 3 amp, 5 amp, 10 amp and 15 amp.
- The MC15 can operate up to 12 fans on a single control.
- Infinite speed adjustment
- Minimum speed adjustment screw.
- Designed to fit a standard 3" x 5" electrical box.
- Mount in a dry location such as the control room.



"FRMC5" CONTROL

- A slide switch is provided to change the direction of the fan from updraft to downdraft.
- 5 amp rating for all reversible models.
- Up to 4 fans can operate on a single control.
- Infinite speed adjustment.
- Minimum speed adjustment screw.
- Designed to fit a standard 3" x 5" electrical box.
- Mount in a dry location such as the control room.



Model Number	Max # of Fans/control	Variable Speed Operation	Power Supply	Ampere Rating	
MC-3	2		120V/1/60HZ	2.5	
MC-5	4	Manual		5.0	
MC-10	8	Manual		10.0	
MC-15	12			15.0	
FRMC5	4	Manual c/w Forward/Reverse Switch		5.0	



Subject to change without notice. 05/12

CANARM LTD. - Corporate Office 2157 Parkedale Ave., PO Box 367 Brockville, ON Canada K6V 5V6 Tel: (613) 342-5424 Fax: 1-800-263-4598 CANARM LTD. - USA Warehouse 808 Commerce Park Drive Ogdensburg, New York, USA 13669 Tel: 1-800-267-4427 Fax: 1-800-263-4598 #7686 Concession 16, RR 4 Arthur, ON Canada NOG 1A0
Tel: (519) 848-3910 Fax: (519) 848-3948