

# Pilot and Signaling Devices

## Heavy-Duty 30.5 mm Watertight/Oiltight Accessories

### CR104P

## Section 9

Accessories, Components and Kits  
600 Volts max. AC/DC  
10 Amperes Continuous



Lamps

#### Lamps

Bulb Type	Voltage	Lamp Type	Description	Product Number
Incandescent with bayonet base	6V	No. 755 Lamp	Transformers and Full-voltage	CR104PXA16
Incandescent with bayonet base	12V	No. 756 Lamp	Full-voltage	CR104PXA12
Incandescent with bayonet base	24V	No. 1819 Lamp	Full-voltage	CR104PXA14
Incandescent with bayonet base	130V		Full-voltage	CR104PXA54
Incandescent with telephone slide base	120V	No. 120PSB Lamp	Full-voltage, 240 V Resistor	CR104PXA52 <sup>1</sup>
Incandescent with bayonet base	60V	No. 1835 Lamp	120V Resistor	CR104PXA15
Incandescent Flasher with bayonet base	6V	No. 267 Lamp	Full-voltage	CR104PXA16F
Incandescent with screw base	6V	No. 1768 Lamp	Cluster light	CR104PXA26
Incandescent with screw base	12V	No. 373 Lamp	Cluster light	CR104PXA22
Incandescent with screw base	24V	No. 399 Lamp	Cluster light	CR104PXA24
Neon with bayonet base	120V	No. NE51H-R Lamp		CR104PXA19

#### Lamps

Bulb Type	Voltage	Lamp Type	Product Number
LED with bayonet base	6 VAC/DC	Flat Top; replaces No. 755 Lamp	080BA9S6L*
LED with bayonet base	12 VAC/DC	Flat Top	080BA9S12L*
LED with bayonet base	24 VAC/DC	Flat Top	080BA9S24L*
LED with bayonet base	48 VAC/DC	Flat Top	080BA9S48L*
LED with bayonet base	120 VAC/DC	Flat Top	080BA9S120L*

\*Insert LED color from table.

#### LED Colors

Colors	Red	Green	Yellow	Orange	White	Blue
*Color code	R	V	G	A	B	L

<sup>1</sup>For replacement only (GO-11GS).

#### Mushroom-Head Caps

Mushroom-Head Cap Diameter	Depth (max. projection front of panel)	Color	Illumination	For Use With	Product Number
1-3/8" (34.9 mm)	1.10" (27.9 mm)	Black	Non-Illuminated	Standard operators	CR104PXM03B
1-3/8" (34.9 mm)	1.10" (27.9 mm)	Red	Non-Illuminated	Standard operators	CR104PXM03R
1-3/8" (34.9 mm)	1.10" (27.9 mm)	Yellow	Non-Illuminated	Standard operators	CR104PXM03E
1-3/8" (34.9 mm)	1.10" (27.9 mm)	Green	Non-Illuminated	Standard operators	CR104PXM03G
1-3/8" (34.9 mm)	1.10" (27.9 mm)	Red	Non-Illuminated	Push-turn operators	CR104PXM04R
2-3/8" (60.3 mm)	1.10" (27.9 mm)	Black	Non-Illuminated	Standard operators	CR104PXM06B
2-3/8" (60.3 mm)	1.10" (27.9 mm)	Red	Non-Illuminated	Standard operators	CR104PXM06R
2-3/8" (60.3 mm)	1.10" (27.9 mm)	Yellow	Non-Illuminated	Standard operators	CR104PXM06E
2-3/8" (60.3 mm)	1.10" (27.9 mm)	Green	Non-Illuminated	Standard operators	CR104PXM06G
1 3/8" (34.9 mm)	1.20" (30.5 mm)	Red	Illuminated	Standard operators	CR104PXL06R
1 3/8" (34.9 mm)	1.20" (30.5 mm)	Yellow	Illuminated	Standard operators	CR104PXL06E
1 3/8" (34.9 mm)	1.20" (30.5 mm)	Green	Illuminated	Standard operators	CR104PXL06G
1 3/8" (34.9 mm)	1.20" (30.5 mm)	Blue	Illuminated	Standard operators	CR104PXL06L
1 3/8" (34.9 mm)	1.20" (30.5 mm)	Amber	Illuminated	Standard operators	CR104PXL06M
3/8" (34.9 mm)	1.20" (30.5 mm)	White	Illuminated	Standard operators	CR104PXL06W
1 3/8" (34.9 mm)	1.20" (30.5 mm)	Clear	Illuminated	Standard operators	CR104PXL06C
1.58" (40.1 mm)	1.58" (40.1 mm)	Black	Non-Illuminated	CR104PTY protected operators	CR104PTYZ152
1.58" (40.1 mm)	1.58" (40.1 mm)	Red	Illuminated, Non-Illuminated	CR104PTY protected operators	CR104PTYZ153
1.58" (40.1 mm)	1.58" (40.1 mm)	Orange	Illuminated, Non-Illuminated	CR104PTY protected operators	CR104PTYZ154
1.58" (40.1 mm)	1.58" (40.1 mm)	Yellow	Illuminated, Non-Illuminated	CR104PTY protected operators	CR104PTYZ155
1.58" (40.1 mm)	1.58" (40.1 mm)	Green	Illuminated, Non-Illuminated	CR104PTY protected operators	CR104PTYZ156
1.58" (40.1 mm)	1.58" (40.1 mm)	Blue	Illuminated, Non-Illuminated	CR104PTY protected operators	CR104PTYZ157
1.58" (40.1 mm)	1.58" (40.1 mm)	White	Illuminated, Non-Illuminated	CR104PTY protected operators	CR104PTYZ158



CR104PXM03\* Mushroom-Head, 1 3/8" dia.



CR104PXM06\* Mushroom-Head, 2 3/8" dia.



CR104PXL06\* Mushroom-Head, 1 3/8" dia., Illuminated



CR104PTZ15\* Replacement heads for 1 protected Mushroom-Heads

