

netSELECT® Products

Decorator Frames

Decorator Products

Features

Decorator frames provide a stylized look for that finishing touch. This allows all devices to match. Multimedia jacks insert into frame for custom configuration.

- Elongated strap for better wall box mounting
- High impact-resistant thermoplastic frame
- UL Listed 1863 - Communication Circuit Accessory and CSA Certified

Decorator Frames



| Color | 1-Gang, 2-Port | 1-Gang, 3-Port | 1-Gang, 4-Port | 1-Gang, 6-Port | 1-Gang, Adapter .406" (10.30) Dia. Hole* | 1-Gang, Adapter Blank** |
|--------------|----------------|----------------|----------------|----------------|--|-------------------------|
| Black | NS612BK | NS613BK | NS614BK | NS616BK | NS621BK | NS620BK |
| Gray | NS612GY | NS613GY | NS614GY | NS616GY | NS621GY | NS620GY |
| Ivory | NS612I | NS613I | NS614I | NS616I | NS621I | NS620I |
| Light Almond | NS612LA | NS613LA | NS614LA | NS616LA | NS621LA | NS620LA |
| White | NS612W | NS613W | NS614W | NS616W | NS621W | NS620W |

Note: *For use with rotary dimmers or to pull through AV or telephone cable.
 **To fill an extra decorator opening or to create customized openings.

Multimedia Face Plates



| Description | 1-Gang, 1-Port Plate | | 1-Gang, 2-Port Plate | | 1-Gang, 3-Port Plate | |
|--------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| | Standard (4.63" x 2.88") | Mid-Size (4.88" x 3.13") | Standard (4.63" x 2.88") | Mid-Size (4.88" x 3.13") | Standard (4.63" x 2.88") | Mid-Size (4.88" x 3.13") |
| Color | | | | | | |
| Black | NSP11BK | NSP101BK | NSP12BK | NSP102BK | NSP13BK | NSP103BK |
| Gray | NSP11GY | NSP101GY | NSP12GY | NSP102GY | NSP13GY | NSP103GY |
| Ivory | NSP11I | NSP101I | NSP12I | NSP102I | NSP13I | NSP103I |
| Light Almond | NSP11LA | NSP101LA | NSP12LA | NSP102LA | NSP13LA | NSP103LA |
| White | NSP11W | NSP101W | NSP12W | NSP102W | NSP13W | NSP103W |



| Description | 1-Gang, 4-Port Plate | | 1-Gang, 6-Port Plate | | 2-Gang, 4-Port Plate | 2-Gang, 6-Port Plate |
|--------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| | Standard (4.63" x 2.88") | Mid-Size (4.88" x 3.13") | Standard (4.63" x 2.88") | Mid-Size (4.88" x 3.13") | Standard (4.63" x 4.69") | Standard (4.63" x 4.69") |
| Color | | | | | | |
| Black | NSP14BK | NSP104BK | NSP16BK | NSP106BK | NSP24BK | NSP26BK |
| Gray | NSP14GY | NSP104GY | NSP16GY | NSP106GY | NSP24GY | NSP26GY |
| Ivory | NSP14I | NSP104I | NSP16I | NSP106I | NSP24I | NSP26I |
| Light Almond | NSP14LA | NSP104LA | NSP16LA | NSP106LA | NSP24LA | NSP26LA |
| White | NSP14W | NSP104W | NSP16W | NSP106W | NSP24W | NSP26W |

Features

Designed to complement decorator styling, these jacks offer voice and Cat. 5e devices to fit within a decorator wallplate.

- High impact-resistant thermoplastic frame
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory and CSA Certified

Molded-In Voice/Low-Speed Data



| Description | Decorative Wallplate, One RJ11 Jack, 6-Position, 4-Conductor | Decorative Wallplate, One RJ11 Jack, 6-Position, 6-Conductor | Decorative Wallplate, Duplex RJ11 Jacks, 6-Position, 6-Conductor | Decorative Wallplate, One Cat. 5e 110 Punch-Down, One RJ11 Jack, 6-Position, 4-Conductor |
|--------------|--|--|--|--|
| Color | Screw Terminations | Screw Terminations | Screw Terminations | Screw Terminations |
| Black | NS770BK | — | — | NS784BK |
| Brown | NS770 | NS771 | — | NS784 |
| Gray | NS770GY | — | — | NS784GY |
| Ivory | NS770I | NS771I | NS772I | NS784I |
| Light Almond | NS770LA | NS771LA | NS772LA | NS784LA |
| White | NS770W | NS771W | NS772W | NS784W |

Features

Coaxial video and combination jacks complement multimedia needs in a 1-gang decorator opening.

- High impact-resistant thermoplastic frame
- Jacks meet FCC part 68
- UL Listed 1863 - Communication Circuit Accessory and CSA Certified

Molded-In Voice/Low-Speed Data



| Description | Decorative Wallplate, Single F-Type Coupler Bulkhead, Female to Female | Decorative Wallplate, Duplex F-Type Coupler Bulkhead, Female to Female | Decorative Wallplate, One RJ11 Jack, 6-Position, 4-Conductor, One F-Type Coupler Bulkhead, Female to Female | Decorative Wallplate, One Cat. 5e 110 Punch-Down, One F-Type Coupler Bulkhead, Female to Female |
|--------------|--|--|---|---|
| Color | Screw Terminations | Screw Terminations | Screw Terminations | Screw Terminations |
| Black | — | — | — | NS785BK |
| Brown | — | — | — | NS785 |
| Gray | — | — | — | NS785GY |
| Ivory | NS780I | NS782I | NS783I | NS785I |
| Light Almond | NS780LA | NS782LA | NS783LA | NS785LA |
| White | NS780W | NS782W | NS783W | NS785W |

Features

Designed for voice, these devices provide an economical alternative to wall phone outlet placement.

- High impact-resistant thermoplastic plate
- Convenient screw down terminals
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory and CSA Certified

Molded-In Plates for Voice



1-Gang Plate,
 One RJ11 Jack,
 6-Position, 4-Conductor,
 Screw Terminations



1-Gang Plate,
 One RJ11 Jack,
 6-Position, 6-Conductor,
 Screw Terminations



1-Gang Plate,
 Duplex RJ11 Jacks,
 6-Position, 4-Conductor,
 Screw Terminations



1-Gang Plate,
 Duplex RJ11 Jacks,
 6-Position, 6-Conductor,
 Screw Terminations

| Description | 1-Gang Plate, One RJ11 Jack, 6-Position, 4-Conductor, Screw Terminations | | 1-Gang Plate, One RJ11 Jack, 6-Position, 6-Conductor, Screw Terminations | | 1-Gang Plate, Duplex RJ11 Jacks, 6-Position, 4-Conductor, Screw Terminations | | 1-Gang Plate, Duplex RJ11 Jacks, 6-Position, 6-Conductor, Screw Terminations | |
|--------------|--|----------|--|----------|--|----------|--|--|
| | Standard | Mid-Size | Standard | Standard | Mid-Size | Standard | Standard | |
| Brown | NS730 | NS735 | NS732 | — | — | — | — | |
| Ivory | NS730I | NS735I | NS732I | NS742I | NS745I | NS744I | — | |
| Light Almond | NS730LA | NS735LA | NS732LA | NS742LA | — | — | — | |
| White | NS730W | NS735W | NS732W | NS742W | NS745W | NS744W | — | |

Molded-In Plates for Voice and CATV/Satellite



1-Gang Plate,
 One F-Type Coupler Bulkhead,
 Female to Female,
 One RJ11 Jack,
 6-Position, 6-Conductor



1-Gang Plate,
 One F-Type Coupler Bulkhead,
 Female to Female,
 One RJ11 Jack,
 6-Position, 4-Conductor



1-Gang Plate,
 One F-Type Coupler Bulkhead,
 Female to Female



1-Gang Plate,
 Duplex F-Type Coupler Bulkhead,
 Female to Female

| Description | 1-Gang Plate, One F-Type Coupler Bulkhead, Female to Female, One RJ11 Jack, 6-Position, 6-Conductor | | 1-Gang Plate, One F-Type Coupler Bulkhead, Female to Female, One RJ11 Jack, 6-Position, 4-Conductor | | 1-Gang Plate, One F-Type Coupler Bulkhead, Female to Female | | 1-Gang Plate, Duplex F-Type Coupler Bulkhead, Female to Female | |
|--------------|---|----------|---|----------|---|----------|--|--|
| | Standard | Mid-Size | Standard | Standard | Mid-Size | Standard | Standard | |
| Ivory | NS748I | NS755I | NS747I | NS750I | NS751I | NS752I | — | |
| Light Almond | NS748LA | NS755LA | NS747LA | NS750LA | NS751LA | NS752LA | — | |
| White | NS748W | NS755W | NS747W | NS750W | NS751W | NS752W | — | |



1-Gang Plate,
 One Cat. 5e 110 Punch-Down
 One RJ11 Jack,
 6-Position, 4-Conductor
 One F-Type Coupler Bulkhead,
 Female to Female

| Description | Standard |
|--------------|----------|
| Black | NS790BK |
| Brown | NS790 |
| Gray | NS790GY |
| Ivory | NS790I |
| Light Almond | NS790LA |
| White | NS790W |