



## CANADIAN WIRETWIST™ CONNECTORS

- Heavy gauge outer shell for superior dielectric performance
- Heat-set, square-cut springs stay in place, and firmly grip wire
- CSA Certified and UL Listed for 600V maximum building wire, and 1000V maximum for signage/fixture applications

**Wire size range** (solid and/or stranded):

- **C3** - 18 to 14 AWG (min. 1x14 + 2x18 / max. 1x10 + 2x14)
- **C4** - 18 to 10 AWG (min. 2x18 / max. 3x14)
- **C6** - 18 to 10 AWG (min. 2x16 + 2x18 / max. 3x10)

CSA 22.2 #188 Certified



**CU/CU ONLY**

| PACKAGE DETAILS / CAT #      | C3                  | C4                  | C6                  |
|------------------------------|---------------------|---------------------|---------------------|
| C-Pak of 100 Connectors      | 30-0C3              | 30-0C4              | 30-0C6              |
| Flip Tub of 500 Connectors   | 30-3C3              | 30-3C4              | 30-3C6              |
| Flip Tub of 1,000 Connectors | 30-4C3              | 30-4C4              | -                   |
| Barrel of Connectors         | 30-6C3 (45K Pieces) | 30-8C4 (25K Pieces) | 30-8C6 (20K Pieces) |

## WIRETWIST™ CU/AL CONNECTORS

### Copper to aluminum connectors

- The only copper to aluminum twist-on connector specifically designed to provide a secure connection while preventing aluminum corrosion
- Pre-filled antioxidant compound prevents oxidation of aluminum conductors
- Swept wings and hexagonal head for easy installation by hand or with standard nut driver
- Live-action, square-wire spring expands and contracts with aluminum wire
- CSA C22.2 #188 Certified



| PACKAGE DETAILS       | CAT #     |
|-----------------------|-----------|
| Card of 15 Connectors | 30-1CCUAL |
| Jar of 75 Connectors  | 30-2CCUAL |
| Jar of 300 Connectors | 30-3CCUAL |

# CONNECTORS