M18™ Multi-Tool Kit

2626-22 (2626-20 Tool-Only)

Specifications:

Speed Settings	12
OPM	11,000 - 18,000
Universal Adapter	Yes
Tool Free Accessory Change	Yes
Length	14"
Weight	4.2 lbs

Includes: (2) M18[™] REDLITHIUM[™] XC Extended Capacity Battery Packs, Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Multi-Voltage Charger, Contractor Bag

M18™ Band Saw Kit

2629-22 (2629-20 Tool-Only)

Specifications:

SFPM	480
Cut Capacity	3-1/4" x 3-1/4"
Shoe	Tool Free
LED Light	Yes
Weight	10.2 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case







Includes: (1) M18[™] REDLITHIUM[™] HIGH DEMAND[™] 9.0 Battery Pack, Blade Wrench, Carbide Tipped Blade, Clamp, Dust Bag, Rapid Charger



M18™ Cut Out Tool Kit

2627-22, 2627-22CT (2627-20 Tool-Only)

Specifications:

RPM	28,000
Tool Free Adjustment	Yes
LED Light	Yes
Belt Clip	Yes
Length	8-9/10"
Weight	1.9 lbs

Includes: 2627-22 (2) M18™ REDLITHIUM™ Extended Capacity XC Battery Packs, Belt Clip, (2) 1/8" Drywall Bits, 1/8" Collet, 1/4" Collet, Wrench, Multi-Voltage Charger, Contractor Bag; **2627-22CT** Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FLEL

Metal Cutting Circular Saw Kit

2782-22 (2782-20 Tool-Only)

Specifications:

RPM	3,900
Blade Size	5-3/8" - 5-7/8"
Arbor Size	20 mm
Hang Hook	Yes
Length	4-7/10"
Weight	6.5 lbs

Includes: (2) M18[™] REDLITHIUM[™] XC5.0 Extended Capacity Battery Packs, 30T Blade, Multi-Voltage Charger, Contractor Bag



M18 FUEL

M18 FUEL

16 Gauge Straight

Finish Nailer Kit 2741-21CT (2741-20 Tool-Only)

Weight

18 Gauge Brad Nailer Kit

2740-21CT (2740-20 Tool-Only)

Specifications:

-	
Nail Diameter	18 gauge
Nail Size	5/8" - 2-1/8"
Nail Collation Angle	0°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Side Load
Length	11-2/5"
Weight	6.1 lbs

Includes: (1) M18[™] REDLITHIUM[™] 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



peomoationsi	
Nail Diameter	16 gauge
Nail Size	1-1/4" - 2-1/2"
Nail Collation Angle	20°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag

M18 FUEL

15 Gauge Finish Nailer Kit

2743-21CT (2743-20 Tool-Only)

Specifications:

specifications.	
Nail Diameter	15 gauge
Nail Size	1-1/4" - 2-1/2"
Nail Collation Angle	34°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



M18 FUEL **Deep Cut Band Saw Kit**

2729-22HD, 2729-22, 2729-21 (2729-20 Tool-Only) Specifications:

SFPM	0 – 380
Cut Capacity	5" x 5"
Shoe	Tool Free
LED Light	Yes
Hang Hook	Yes
Weight	15.9 lbs

Includes: 2729-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Blade, Rapid Charger, Carrying Case; 2729-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2729-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger









Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



M18 FUEL

7" Variable Speed Polisher Kit

2738-22, 2738-22P (2738-20 Tool-Only)

Specifications:

Capacity	7" Maximum
RPM	0 – 2,200
Variable Speed Dial and Trigger	Yes
Lock-On / Lock-Off	Yes
Length	19-4/5"
Weight	6.4 lbs

Includes: 2738-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Backing Pad, Screen Cover, Side Handle, Bail Handle with (2) Bolts, Rapid Charger; 2738-22P Includes 7" Wool Cutting Pad, 7" Yellow Foam Polishing Pad, 7" Black Foam Finishing Pad




M18 FUEL 4-1/2" / 5" Grinder **Paddle Switch, No-Lock Kit**

2780-22HD, 2780-22, 2780-21 (2780-20 Tool-Only)

Specifications	:	
RPM	8,500	
Switch Type	Paddle No-Lock	
Power to Grind	Yes	
Overload Protection	Yes	
Electronic Clutch	Yes	
Tool Free Accessory Change and Guard	Yes	
Length	15"	
Weight	8.2 lbs	

Includes: 2780-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; 2780-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2780-21 Includes (1) M18[™] REDLITHIUM[™] XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger





4-1/2" / 5" Grinder Slide Switch, Lock-On Kit 2781-22HD, 2781-22, 2781-21 (2781-20 Tool-Only)

Specifications:

	-
RPM	8,500
Switch Type	Slide with Lock-On
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change and Guard	Yes
Length	15"
Weight	8.2 lbs

Includes: 2781-22HD (2) $M18^{TM}$ REDLITHIUMTM HIGH DEMANDTM 9.0 Battery Packs, Rapid Charger, Carrying Case; 2781-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2781-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18 FUEL 4-1/2" / 5" Braking **Grinder Kit**

2783-22HD, 2783-22 (2783-20 Tool-Only Specifications:

	(-3)
RPM	8,500
Switch Type	Paddle No-Lock
Brake	Yes
Clutch	Yes
Overload Protection	Yes
Tool Free Accessory Change and Guard	FIXTEC™ Nut and Tool Free Guard
Length	15-1/4"
Weight	8.2 lbs

Includes: 2783-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, FIXTEC™ Nut, Flange Nut, T1 Guard, T27 Guard, Rapid Charger, Carrying Case; **2783-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger



1/4" Die Grinder Kit

2784-22 (2784-20 Tool-Only)

Specifications:

Collet Size	1/4"
RPM	20,000
Switch Type	Slide, Lock-On
Length	18"
Weight	4.6 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, 11/16" Wrench, 1/2" Wrench, Multi-Voltage Charger, Carrying Case



M18[™] 18 Gauge Double Cut Shear Kit

2635-22 (2635-20 Tool-Only)

Specifications:

	5.1
Head	18 Gauge Double Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	17-1/4"
Weight	5.6 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs. Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag



Specifications:

RPM

I II IVI	3,000
Switch	Paddle
Guard Adjustment	Tool Free
Overload Protection	Yes
Weight	5.9 lbs

Includes: (2) M18[™] REDLITHIUM[™] XC Extended Capacity Battery Packs, Type 1 Guard, Type 27 Guard, Spanner Wrench, Side Handle, Multi-Voltage Charger, Contractor Bag

M18™ 14 Gauge **Double Cut Shear Kit**

2636-22 (2636-20 Tool-Only)

Specifications:

Head	14 Gauge Double Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	17-1/4"
Weight	6.2 lbs

Includes: (2) M18[™] REDLITHIUM[™] XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag



Specifications:

-	
Head	18 Gauge Single Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	18"
Weight	5.8 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag



