

## SL3—OUT DIFFUSION LED STRIP — OUTDOOR

### DESCRIPTION

Diffusion LED SL-3 is a flexible 10mm linear LED strip. Available in lengths of 16ft or 32ft, it may be cut every 6 LEDs (50mm / 2"). It uses 120 LEDs per Meter (36 LEDs per ft)

### FEATURES

- \* Includes endcaps and mounting clips with screws
- \* Long life LED: 50,000 hours
- \* Dimmable with dimming power supply
- \* 24" leads on both ends of each roll
- \* IP65

\*custom lengths available upon request\*

### SPECIFICATIONS

LED: 10 watts/Meter (3 watts/ft)  
LAMP LIFE: 50,000 hours LM80  
POWER INPUT: 24V DC  
CRI > 91

### LUMENS

2700K = 788 lm/M (236 lm/ft)  
3000K = 820 lm/M (252 lm/ft)  
3400K = 876 lm/M (263 lm/ft)  
4100K = 908 lm/M (279 lm/ft)



ORDERING  
CODE

LENGTH

VOLTAGE

COLOR

SL3-OUT	16	24V	2700
SL3-OUT	16 ft 32 ft	24 Volt	2700 K 3000 K 3400 K 4100 K

Project: \_\_\_\_\_  
Type: \_\_\_\_\_  
Date: \_\_\_\_\_  
Part #: \_\_\_\_\_