

M18 FUEL
1/2" Hammer Drill/Driver w/ ONE-KEY™ Kit

2706-22 (2706-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
BPM	0 – 32,000
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/5"
Weight	4.9 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Hammer Drill/Driver Kit

2607-22, 2607-22CT (2607-20 Tool-Only)

Specifications:

Peak Torque	525 in-lbs
RPM	0 – 450 / 0 – 1,800
BPM	0 – 28,800
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/4"
Weight	4.5 lbs

Includes: **2607-22** (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case; **2607-22CT** Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL
1/2" Hammer Drill/Driver Kit

2704-22 (2704-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
BPM	0 – 32,000
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/4"
Weight	4.9 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18 FUEL
1/2" Drill/Driver w/ ONE-KEY™ Kit

2705-22 (2705-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-1/5"
Weight	4.8 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18 FUEL
1/2" Drill/Driver Kit

2703-22 (2703-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
Chuck type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-1/2"
Weight	4.9 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Compact Brushless Drill/Driver Kit

2701-22CT (2701-20 Tool-Only)

Specifications:

Peak Torque	500 in-lbs
RPM	0 – 450 / 0 – 1,800
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	6-7/8"
Weight	3.7 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Compact Drill/Driver Kit

2606-22CT (2606-20 Tool-Only)

Specifications:

Peak Torque	500 in-lbs
RPM	0 – 450 / 0 – 1,800
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-1/4"
Weight	3.8 lbs

Includes: (2) M18™ REDLITHIUM™ Compact Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 3/8" Right Angle Drill/Driver Kit

2615-21, 2615-21CT (2615-20 Tool-Only)

Specifications:

Peak Torque	125 in-lbs
RPM	0 – 1,500
Clutch Settings	11 Settings plus Drill Mode
Chuck Type	3/8" Single Sleeve
Head Profile	3-3/4"
Weight	4.3 lbs

Includes: **2615-21** (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack, Multi-Voltage Charger, Carrying Case; **2615-21CT** Includes (1) M18™ REDLITHIUM™ Compact Battery Pack



M18 FUEL
Drywall Screw Gun Kit

2866-22, 2866-22CT (2866-20 Tool-Only)

Specifications:

RPM	0 – 4,500
Belt Clip	Yes
Auto Start Mode	Yes
Length	9"
Weight	4.1 lbs

Includes: **2866-22** (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, PR2 Bit, Multi-Voltage Charger, Contractor Bag; **2866-22CT** Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



Related Accessory:
49-20-0001 MILWAUKEE® Collated Magazine
Screw Capacity: Up to 2"
Compatible with all major screw brands



M18 FUEL

HOLE HAWG® Right Angle Drill Kit w/ QUIK-LOK™

2708-22HD, 2708-22 (2708-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length	17"
Weight	9.3 lbs



Includes: 2708-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; **2708-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger

M18 FUEL

HOLE HAWG® 1/2" Right Angle Drill Kit

2707-22HD, 2707-22 (2707-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	1/2" Metal Keyed
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length	17"
Weight	9.8 lbs



Includes: 2707-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Chuck Key, Rapid Charger, Carrying Case; **2707-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger

M18 FUEL

SUPER HAWG™ Right Angle Drill Kit w/ QUIK-LOK™

2711-22HD, 2711-22 (2711-20 Tool-Only)

Specifications:

RPM	0 – 350 / 0 – 950
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6"
Mechanical Clutch	Yes
Length	22"
Weight	14.8 lbs



Includes: 2711-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Side Handle, Rapid Charger, Contractor Bag; **2711-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs

M18 FUEL

SUPER HAWG™ 1/2" Right Angle Drill Kit

2709-22HD, 2709-22 (2709-20 Tool-Only)

Specifications:

RPM	0 – 350 / 0 – 950
Chuck Type	1/2" Metal Keyed
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6"
Mechanical Clutch	Yes
Length	22"
Weight	14.9 lbs



Includes: 2709-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Chuck Key, Side Handle, Rapid Charger, Contractor Bag; **2709-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs


M18 FUEL

1-1/2" Magnetic Drill Kit

2787-22HD

Specifications:

Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13-3/4" x 7-1/2" x 15-1/2"
Weight	30.4 lbs



Includes: (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, Rapid Charger, Carrying Case


M18 FUEL

1-1/2" Lineman Magnetic Drill Kit

2788-22HD

Specifications:

Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13-3/4" x 7-1/2" x 15-1/2"
Weight	30.4 lbs



Includes: (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, AC/DC Wall and Vehicle Charger, Carrying Case



M18 FUEL

1-9/16" SDS Max Rotary Hammer Kit

2717-22HD (2717-20 Tool-Only)

Specifications:

RPM	0 – 440
BPM	0 – 3,000
Impact Energy	5.0 ft-lbs
2-Mode Operation	Rotary Hammer and Hammer Only
Weight	13.75 lbs



Includes: (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Side Handle, Depth Rod, Rapid Charger, Carrying Case

Related Accessory: **2306-22** M12™ HAMMERVAC™ Universal Dust Extractor


M18 FUEL

1-1/8" SDS Plus Rotary Hammer Kit

2715-22HD, 2715-22, 2715-22DE (2715-20 Tool-Only)

Specifications:

RPM	0 – 1,350
BPM	0 – 5,000
Impact Energy	3.3 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	10.1 lbs



Includes: 2715-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Slide Handle, Depth Rod, Rapid Charger, Carrying Case; **2715-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; **2715-22DE** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger


HAMMERVAC™

Dedicated Dust Extractor

2715-DE

Specifications:

Compatibility	For use with 2715-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"



Includes: Replacement Nozzle and HEPA Filter

M18 FUEL

1" SDS Plus Rotary Hammer Kit

2712-22HD, 2712-22, 2712-22DE (2712-20 Tool-Only)

Specifications:

RPM	0 – 1,400
BPM	0 – 4,900
Impact Energy	1.7 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	9.4 lbs



Includes: 2712-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Slide Handle, Depth Rod, Rapid Charger, Carrying Case; **2712-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; **2712-22DE** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger

HAMMERVAC™

Dedicated Dust Extractor

2712-DE

Specifications:

Compatibility	For use with 2712-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"



Includes: Replacement Nozzle and HEPA Filter

M18 FUEL

1" SDS Plus D-Handle Rotary Hammer Kit

2713-22HD, 2713-22 (2713-20 Tool-Only)

Specifications:

Capacity	1"
Impact Energy	2.15 ft-lbs
RPM	0 – 1,500
BPM	0 – 4,400
Length	16-1/2"
Weight	8.5 lbs




Includes: 2713-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Slide Handle, Depth Rod, Rapid Charger, Carrying Case; **2713-22** Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger

M18™ 7/8" SDS Plus Rotary Hammer Kit

2605-22 (2605-20 Tool-Only)

Specifications:

RPM	0 – 1,400
BPM	0 – 4,800
Impact Energy	1.4 ft-lbs
3-Mode Operation	Hammer Only, Rotary Hammer and Rotation Only
Weight	7.2 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case


Related Accessory: **2306-22** M12™ HAMMERVAC™ Universal Dust Extractor

M18™ 5/8" SDS Plus Rotary Hammer Kit

2612-22, 2612-21 (2612-20 Tool-Only)

Specifications:

RPM	0 – 1,300
BPM	0 – 7,000
Impact Energy	1.0 ft-lbs
2-Mode Operation	Rotary Hammer and Rotation Only
Weight	5.5 lbs



Includes: 2612-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case; **2612-21** Includes (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack

Related Accessory: **2306-22** M12™ HAMMERVAC™ Universal Dust Extractor

