

M18 FUEL
7" Variable Speed Polisher Kit

2738-22, 2738-22P (2738-20 Tool-Only)

Specifications:

Capacity	7" Maximum
RPM	0 – 2,200
Variable Speed Dial and Trigger	Yes
Lock-On / Lock-Off	Yes
Length	19-4/5"
Weight	6.4 lbs



Includes: 2738-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Backing Pad, Screen Cover, Side Handle, Bail Handle with (2) Bolts, Rapid Charger; 2738-22P Includes 7" Wool Cutting Pad, 7" Yellow Foam Polishing Pad, 7" Black Foam Finishing Pad



M18 FUEL
4-1/2" / 5" Grinder Paddle Switch, No-Lock Kit

2780-22HD, 2780-22, 2780-21 (2780-20 Tool-Only)

Specifications:

RPM	8,500
Switch Type	Paddle No-Lock
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change and Guard	Yes
Length	15"
Weight	8.2 lbs



Includes: 2780-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; 2780-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2780-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18 FUEL
4-1/2" / 5" Grinder Slide Switch, Lock-On Kit

2781-22HD, 2781-22, 2781-21 (2781-20 Tool-Only)

Specifications:

RPM	8,500
Switch Type	Slide with Lock-On
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change and Guard	Yes
Length	15"
Weight	8.2 lbs



Includes: 2781-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; 2781-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2781-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18 FUEL
4-1/2" / 5" Braking Grinder Kit

2783-22HD, 2783-22 (2783-20 Tool-Only)

Specifications:

RPM	8,500
Switch Type	Paddle No-Lock
Brake	Yes
Clutch	Yes
Overload Protection	Yes
Tool Free Accessory Change and Guard	FIXTEC™ Nut and Tool Free Guard
Length	15-1/4"
Weight	8.2 lbs



Includes: 2783-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, FIXTEC™ Nut, Flange Nut, T1 Guard, T27 Guard, Rapid Charger, Carrying Case; 2783-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger

M18 FUEL
1/4" Die Grinder Kit

2784-22 (2784-20 Tool-Only)

Specifications:

Collet Size	1/4"
RPM	20,000
Switch Type	Slide, Lock-On
Length	18"
Weight	4.6 lbs



Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, 11/16" Wrench, 1/2" Wrench, Multi-Voltage Charger, Carrying Case



M18™ 18 Gauge Double Cut Shear Kit

2635-22 (2635-20 Tool-Only)

Specifications:

Head	18 Gauge Double Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	17-1/4"
Weight	5.6 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag



M18™ 4-1/2" Cut-Off / Grinder Kit

2680-22 (2680-20 Tool-Only)

Specifications:

RPM	9,000
Switch	Paddle
Guard Adjustment	Tool Free
Overload Protection	Yes
Weight	5.9 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Type 1 Guard, Type 27 Guard, Spanner Wrench, Side Handle, Multi-Voltage Charger, Contractor Bag

M18™ 14 Gauge Double Cut Shear Kit

2636-22 (2636-20 Tool-Only)

Specifications:

Head	14 Gauge Double Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	17-1/4"
Weight	6.2 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag



M18™ 18 Gauge Single Cut Shear Kit

2637-22 (2637-20 Tool-Only)

Specifications:

Head	18 Gauge Single Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	18"
Weight	5.8 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag

M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Fixed BG Die

2678-22BG

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed BG Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag



M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Fixed O Die

2678-22O

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed O Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Snub Nose

2678-22

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Snub Nose Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

M18™ FORCE LOGIC™ 6T Crimper Kit w/ Kearney Grooves

2678-22K

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Kearney Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

M18™ FORCE LOGIC™ 6T Crimper Accessories

Compatible with 2678-22BG, 2678-22O, 2678-22, 2678-22K

6T Utility Crimper Jaws

- 49-16-BGD3 6T Fixed BG Crimping Jaw;
- 49-16-0OD3 6T Fixed O Crimping Jaw;
- 49-16-00D3 6T Snub Nose Crimping Jaw;
- 49-16-KEAR 6T Kearney Crimping Jaw

W Style Dies

- 49-16-WBG0 W Style Die: "W-BG";
- 49-16-WO00 W Style Die: "W-O";
- 49-16-WC00 W Style Die: "W-C";
- 49-16-W840 W Style Die: "W-K840";
- 49-16-W161 W Style Die: "W-161";
- 49-16-W162 W Style Die: "W-162";
- 49-16-W163 W Style Die: "W-163";
- 49-16-W165 W Style Die: "W-165";
- 49-16-W166 W Style Die: "W-166";
- 49-16-W243 W Style Die: "W-243";
- 49-16-W247 W Style Die: "W-247";
- 49-16-W249 W Style Die: "W-249";
- 49-16-W164 W Style Die: "W-164";
- 49-16-W237 W Style Die: "W-237";
- 49-16-W239 W Style Die: "W-239"



M18™ FORCE LOGIC™ 600 MCM Crimper Kit

2679-22

Specifications:

UL Classification	Yes (All 7 Manufacturers)
Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 600 MCM Commercial U Crimping Jaw, Multi-Voltage Charger, Carrying Case

Related Accessories:

49-16-U000 600 MCM Crimping Jaw

Accessory Kits

- 49-16-KITA #8 AWG – 350 MCM Aluminum U Style Die Kit;
- 49-16-KITC #8 AWG – 600 MCM Copper U Style Die Kit

Copper U Style Dies

- 49-16-U008C #8 Copper 12T U Style Die;
- 49-16-U006C #6 Copper 12T U Style Die;
- 49-16-U004C #4 Copper 12T U Style Die;
- 49-16-U002C #2 Copper 12T U Style Die;
- 49-16-U001C #1 Copper 12T U Style Die;
- 49-16-U01AC 1/0 Copper 12T U Style Die;
- 49-16-U02AC 2/0 Copper 12T U Style Die;
- 49-16-U03AC 3/0 Copper 12T U Style Die;
- 49-16-U04AC 4/0 Copper 12T U Style Die;
- 49-16-U250C 250 MCM Copper 12T U Style Die;
- 49-16-U300C 300 MCM Copper 12T U Style Die;
- 49-16-U350C 350 MCM Copper 12T U Style Die;
- 49-16-U400C 400 MCM Copper 12T U Style Die;
- 49-16-U500C 500 MCM Copper 12T U Style Die;
- 49-16-U600C 600 MCM Copper 12T U Style Die

Aluminum Dual Rated U Style Dies

- 49-16-U008 #8 Aluminum 12T U Style Die;
- 49-16-U006 #6 Aluminum 12T U Style Die;
- 49-16-U004 #4 Aluminum 12T U Style Die;
- 49-16-U002 #2 Aluminum 12T U Style Die;
- 49-16-U001 #1 Aluminum 12T U Style Die;
- 49-16-U01A 1/0 Aluminum 12T U Style Die;
- 49-16-U02A 2/0 Aluminum 12T U Style Die;
- 49-16-U03A 3/0 Aluminum 12T U Style Die;
- 49-16-U04A 4/0 Aluminum 12T U Style Die;
- 49-16-U250 250 MCM Aluminum 12T U Style Die;
- 49-16-U300 300 MCM Aluminum 12T U Style Die;
- 49-16-U350 350 MCM Aluminum 12T U Style Die;
- 49-16-U400 400 MCM Aluminum 12T U Style Die;
- 49-16-U500 500 MCM Aluminum 12T U Style Die;
- 49-16-U600 600 MCM Aluminum 12T U Style Die

M18™ FORCE LOGIC™ 12T Utility Crimper Kit

2778-22

Specifications:

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16"
Weight	11.9 lbs



Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, AC/DC Wall and Vehicle Charger, Carabiner, Utility Bag

M18™ FORCE LOGIC™ 750 MCM Crimper Kit

2779-22

Specifications:

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16"
Weight	11.5 lbs



Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Carrying Case

Related Accessories:

Accessory Kits

- 49-12-KITC EXACT™ #6 AWG – 750 MCM Cu 12T U Style Die Kit;
- 49-12-KITA EXACT™ #6 AWG – 750 MCM Al 12T U Style Die Kit

EXACT™ 12T Copper U Style Dies

- 49-12-U008C #8 Copper 12T U Style Die;
- 49-12-U006C #6 Copper 12T U Style Die;
- 49-12-U004C #4 Copper 12T U Style Die;
- 49-12-U002C #2 Copper 12T U Style Die;
- 49-12-U001C #1 Copper 12T U Style Die;
- 49-12-U01AC 1/0 Copper 12T U Style Die;
- 49-12-U02AC 2/0 Copper 12T U Style Die;
- 49-12-U03AC 3/0 Copper 12T U Style Die;
- 49-12-U04AC 4/0 Copper 12T U Style Die;
- 49-12-U250C 250 MCM Copper 12T U Style Die;
- 49-12-U300C 300 MCM Copper 12T U Style Die;
- 49-12-U350C 350 MCM Copper 12T U Style Die;
- 49-12-U400C 400 MCM Copper 12T U Style Die;
- 49-12-U500C 500 MCM Copper 12T U Style Die;
- 49-12-U600C 600 MCM Copper 12T U Style Die;
- 49-12-U750C 750 MCM Copper 12T U Style Die

EXACT™ 12T Aluminum U Style Dies

- 49-12-U008 #8 Aluminum 12T U Style Die;
- 49-12-U006 #6 Aluminum 12T U Style Die;
- 49-12-U004 #4 Aluminum 12T U Style Die;
- 49-12-U002 #2 Aluminum 12T U Style Die;
- 49-12-U001 #1 Aluminum 12T U Style Die;
- 49-12-U01A 1/0 Aluminum 12T U Style Die;
- 49-12-U02A 2/0 Aluminum 12T U Style Die;
- 49-12-U03A 3/0 Aluminum 12T U Style Die;
- 49-12-U04A 4/0 Aluminum 12T U Style Die;
- 49-12-U250 250 MCM Aluminum 12T U Style Die;
- 49-12-U300 300 MCM Aluminum 12T U Style Die;
- 49-12-U350 350 MCM Aluminum 12T U Style Die;
- 49-12-U400 400 MCM Aluminum 12T U Style Die;
- 49-12-U500 500 MCM Aluminum 12T U Style Die;
- 49-12-U600 600 MCM Aluminum 12T U Style Die;
- 49-12-U750 750 MCM Aluminum 12T U Style Die

