

LED STEP LIGHTS

5w 3000K color temperature with 84+ CRI and a 120° beam spread. LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox.



P6827-0930K



P6827-3030K



P6828-0930K



P6828-2030K



P6828-3030K



P6828-3130K



P6829-2030K



P6829-0930K



P6832-0930K



P6832-3130K

P6827-0930K Brushed Nickel
P6827-2030K Antique Bronze
P6827-3030K White
P6827-3130K Black
 Louvered horizontal step/wall light.
 Wet location listed.
 5-1/4" W., 3-1/2" ht.
 5w LED module included.

P6828-0930K Brushed Nickel
P6828-2030K Antique Bronze
P6828-3030K White
P6828-3130K Black
 Louvered vertical step/wall light.
 Wet location listed.
 3-1/2" W., 5-1/4" ht.
 5w LED module included.

P6829-0930K Brushed Nickel
P6829-2030K Antique Bronze
P6829-3030K White
P6829-3130K Black
 Vertical step/wall light.
 Wet location listed.
 2-3/4" W., 4-1/2" ht.
 5w LED module included.

P6832-0930K Brushed Nickel
P6832-2030K Antique Bronze
P6832-3030K White
P6832-3130K Black
 Horizontal step/wall light.
 Wet location listed.
 2-7/8" ht., 4-1/2" W.
 5w LED module included.