



S9400

7PAR20/LED/25'/2700K/120V/D
7 watt PAR20 LED; 2700K; 25' beam spread; Medium base;
120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Leviton® 6674
- Leviton® IPL06
- Lutron® Nova T NYCL-250
- Lutron® SELV300
- Lutron® SLV600P



S9400

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9400	045923094002	120	7	50W	PAR20	Medium	E26

Lamp Code	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
7PAR20/LED/25'/2700K/120V/D	Silver	3 1/32"	2.50"	500	25000	2700	Warm White

CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed	Warranty
80	25	24/6	Box	ENERGY STAR	Yes	Yes	3 Years