



Siemens Low Voltage Molded Case Circuit Breakers Sentron Molded Case Circuit Breakers - Enclosed Circuit Breakers are Circuit Protection Molded Case Circuit Breakers. Sub Brand: SENTRON Type: MD6 Std: UL V. Rating: 600V A. Rating: 800A F. Rating: 50/60Hz Frame: MD Trip Type: THERMAL MAGNETIC Interrupt Rating: 25KA No. Of Poles: 3P Enclosure: TYPE 1S L: 64 W: 32 H: 12 Operating Temperature: (-25C -- 75C) AMBIENT TEMPERATURE

Number of poles	3
-----------------	---

Environmental conditions

Ambient condition for operation	INDOOR
Ambient temperature during operation maximum	75 °C
Ambient temperature during operation minimum	-25 °C

Model

Product brand name	Siemens
--------------------	---------

Mechanical Design

Design of the housing	TYPE 1S
Design of the overload release	THERMAL MAGNETIC
Design of the product	MD6
Size of the circuit-breaker	MD

General product approval

Standard	UL
last modified:	05/28/2019