













ECS Selector Switch Control Stations

Explosionproof, Dust-Ignitionproof, Factory Sealed and Non-Factory Sealed

CEC:






Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1 and 2, Groups E, F, G
Class III
CSA Type 3R, 7BCD, 9EFG

		Description	Left	Diagram Centre	Right	Legend Plate	Catalog Number
Selector Switches ② – Factory Sealed – Cover Assembly Only							
 2 Position	 3 Position	2 Position 2 Circuit		None		Start/Stop	ECSK12
		2 Position 4 Circuit		None		Start/Stop	ECSK35
		3 Position 2 Circuit				Hand/Off/Auto	ECSK102
		3 Position 4 Circuit				Hand/Off/Auto	ECSK345

Key-Operated Selector Switches – Non-Factory Sealed – Cover Assembly Only

Key removable in one position.



2 Position 2 Circuit		None		Start/Stop	ECSKSA82U
3 Position 4 Circuit				Hand/Off/Auto	ECSKSA86U

Type	Catalog Number	
	Front Operated	Key Operated

Toggle Switches ① ③ – Cover Assembly Only – No Motor Ratings



ECSKF1



ECSKK1

20 Amp 120/277 Vac, Factory Sealed

1-Pole	ECSKF1	ECSKK1
2-Pole	ECSKF2	ECSKK2
3 Way	ECSKF3W	ECSKK3W

20 Amp 120/277 Vac, Non-Factory Sealed

4 Way	ECSKF4W	ECSKK4W
-------	---------	---------



ECSKF17



ECSKK17

20 Amp 347 Vac, Non-Factory Sealed

1-Pole	ECSKF17	ECSKK17
2-Pole	ECSKF27	ECSKK27
3 Way	ECSKF3W7	ECSKK3W7
4 Way	ECSKF4W7	ECSKK4W7



ECSKF13



ECSKK13

30 Amp 120/277 Vac – Non-Factory Sealed

1-Pole	ECSKF13	ECSKK13
2-Pole	ECSKF23	ECSKK23
3 Way	ECSKF3W3	ECSKK3W3
3-Pole	ECSKF33	ECSKK33

① Suitable for use as a motor disconnect.

② 3 Position selector switch spring return from right: add suffix -S634. 3 Position selector switch spring return from left: add suffix -S635.

③ Optional flush mounted single LED indicator light - add suffix -LED.