

LED STRING LIGHTS

- 5000K Light Color Temperature
- 800 Lumens per head
- 5-15 plug + receptacle
- IP65
- 100 Lumens of uplight
- 700 Lumens of down light



7164SW

Description	Model #	Cord Type	Head Count	Linkable Units	Weight
50' - 14/3, 4,000 Lumen, LED String Light	7164SW	14/3 SJTW	5	20	
100' - 14/3, 8,000 Lumen, LED String Light	7165SW	14/3 SJTW	10	10	

STRING LIGHTS WITH PLASTIC CAGE, 120V

- Medium base, A-23 sockets



7145SW

Description	Model #	Cord Type	Socket #	Linkable Units	Weight
100' - 14/2, Medium Duty String Light with Plastic Cage	7145SW	14/2 SJTW	10	-	
50' - 14/3, Medium Duty String Light with Plastic Cage	11107050	14/3 SJTW	5	8	10 lbs
100' - 14/3, Medium Duty String Light with Plastic Cage	11107100	14/3 SJTW	10	5	20 lbs
50' - 12/3, Heavy Duty String Light with Plastic Cage	7548SW	12/3 SJTW	5		
100' - 12/3, Heavy Duty String Light with Plastic Cage	7549SW	12/3 SJTW	10		

STRING LIGHTS WITH LED BULBS AND PLASTIC CAGE, 120V

- 1,500 lumens bulbs
- Medium base, A-23 socket
- 30,000 Hr. bulb life



111100

Description	Model #	Cord Type	Socket #	Linkable Units	Weight
50' - 14/3, Heavy Duty String Light with Plastic Cage and 1,500 Lumen Bulbs	131050	14/3 SJTW	5	8	10 lbs
100' - 14/3, Heavy Duty String Light with Plastic Cage and 1,500 Lumen Bulbs	131100	14/3 SJTW	10	5	20 lbs
100' - 14/2, Heavy Duty String Light with Plastic Cage and 1,500 Lumen Bulbs	111100	14/2 SJTW	10	-	20 lbs

STRING LIGHTS WITH METAL CAGE, 120V

- Medium base, A-23 sockets
- STW options with extra hard cable projection
- Meets OSHA and NEC requirements



7538SW

Description	Model #	Cord Type	Socket #	Linkable Units	Bottom Cage Shield	Weight
50' - 12/3, Medium Duty String Light with Metal Cage	7538SW	12/3 SJTW	5		No	
100' - 12/3, Medium Duty String Light with Metal Cage	7539SW	12/3 SJTW	10		No	
50' - 12/3, Heavy Duty String Light with Metal Cage	11109050	12/3 STW	5	5	Yes	13 lbs
100' - 12/3, Heavy Duty String Light with Metal Cage	11109100	12/3 STW	10	5	Yes	28 lbs