

RL992

9" Round LED Slim Surface Mount Dimmable
Fixture with Easy Color SeleCCTor

1/2" Thick Surface LED Fixture

Catalog Number:

Project Name:

Note:

Type:



FIELD SELECTABLE CCT SLIM SURFACE MOUNT DOWNLIGHT



ENGINEERED FOR VERSATILITY AND PERFORMANCE

The Elite LED Slim Surface Mount has been engineered to install into most standard junction boxes. Up to 1500 usable lumens are directed from the luminaire to the work surface. Lighting is smooth and comfortable, all while using 75% less energy than the equivalent Incandescent. Features 50,000 hours of life, and California Title-24 compliance.

OPTICS

The Elite LED Module system is much more than just a simple LED retrofit. The Elite LED system is a highly engineered work of design and optical science which produces up to 1500 lumens. Our meticulously crafted optics gather the light scattered by the LED chip and shape it into a functional beam with uniform light distribution.

DIMMING

Intended for Triac (120V) base on configuration. Minimum 90° supply conductors.

WARRANTY


The Elite LED lighting system carries a five-year carefree warranty for parts and components. (Labor not included)



SPECIFICATIONS:

APERTURE	9"
DELIVERED LUMENS	1500 lumens
WATTAGE	18W
LUMEN/WATT	83
CCT	(Easy Color SeleCCTor - 30K / 40K / 50K)
CRI	90
VOLTAGE	120V
POWER FREQUENCY	50/60 Hz
FINISH	White
AMBIENT ENVIRONMENT	Damp location

Compatible Junction Boxes:



Note: A 2-1/8" deep octagon junction box is recommended for through circuit wiring applications.

Ordering Information: Example: RL992-1500L-DIMTR-120-30K/40K/50K-90-WH

<div> </div>	<div> </div>	<div> </div>	<div> </div>	<div> </div>	<div> </div>	<div> </div>
SERIES/APERTURE/LUMENS	DIMMING	VOLTAGE	CCT	CRI	FINISH	TRIM INSERT
RL992-1500L - 9" aperture/1500 lumens	DIMTR - Triac	120 - 120V	30K/40K/50K - 3000K/4000K/5000K	90 - 90	WH - White BZ - Bronze BN - Brushed Nickel	RL992-RT-BK - Black RL992-RT-BN - Brushed Nickel RL992-RT-BZ - Bronze RL992-RT-CH - Chrome