



SPEC GRADE TYPE C USB CHARGING RECEPTACLE - WHITE

TR20USBCCW | [Pass & Seymour](#)

FEATURES & BENEFITS

Pass & Seymour Commercial Specification and Hospital Grade USB Charging Receptacles are designed for the commercial market, and can withstand heavy use due to their UL Fed Spec certification. Features include an improved overall 3.1A USB charging output with current-sharing technology, USB Type-A and USB Type-C charging ports, auto-ground clips, and tamper-resistant receptacles. Posted terminal screws and external pressure plates allow for faster, easier, and more reliable back- and side-wire terminations.



- Available with one USB Type-A and one USB Type-C port or two USB Type-C ports to charge the latest mobile devices
- Overall 3.1A charging capability with smart current-sharing technology to allow for full 3.1A through a single port
- Slim design allows for installation in standard-depth wall boxes
- Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations
- Patented tamper-resistant shutters on receptacles help prevent improper insertion of foreign objects
- Available in 15 and 20A, 125V Specification and Hospital Grade versions

SPECIFICATIONS

GENERAL INFO

Color: White

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CSA C22.2 No. 42, CSA, C22.2 No. 223

cULus: Yes

UL Standard: complies with test requirements UL498, UL1310, Fed Spec WC-596

DIMENSIONS

Depth (US): 1.425"

Height (US): 3.28"

Width (US): 1.693"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

RatedVoltage: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA