

## Standard & HD Power Video Balun

Power / Video Baluns

Single channel passive transceiver

Voltage: 12V~50V (AC RMS/DC) 4.5A (AC RMS/DC).

Power Input & Surge Protection LED Light,

Standard Video distance over 2250 ft

Reduced Video distances when using CVI, TVI, MPX technology.

Color HD video HD-CVI/TVI/MPX 720P up 75M / 250ft

Color HD video HD-CVI/TVI/MPX 1080P up 50M / 160ft

Power Distance dependent on input voltage and voltage



AZBLN217



AZBLN219



- 4ch Balun
- 3ft Power leads
- 3ft Video leads

### AZBLN217 POWER VIDEO BALUN



## AZBLN217

**Passive Video and Power Transceiver,**  
1CH, Voltage: 12V~50V (AC RMS/DC) 4.5A (AC  
RMS/DC). Power Input & Surge Protection LED Light,  
Video distance over 2250 ft, Power Distance  
dependent on input voltage and voltage drop. (PAIR)

Voltage Drop According to Cable Length (24AWG):

Transmission Distance	Transmission Voltage (12V DC, 0.5A)	Transmission Voltage (12V DC, 1A)	Transmission Voltage (12V DC, 1.5A)
50M / 160Ft	13.5V	15.5V	17.0V
100M / 320Ft	15.5V	18.5V	22.0V
150M / 500Ft	17.0V	22.0V	27.0V
200M / 650Ft	18.5V	25.5V	32.0V