

**M12™ ROCKET™ Dual Power Tower Light**

2132-20 Tool-Only

**Specifications:**

Lumens	1,400 / 700
Modes	High, Low
Powered By	M12™ or Corded
Height	30.5" Collapsed, 5' 8" Fully Extended
Weight	6.7 lbs



POWERED BY



Battery and Charger Sold Separately



**M12™ Metal Flashlight Kit**

2355-21 (2355-20 Tool-Only)

**Specifications:**

Lumens	800 / 325 / 800
Modes	High, Medium, Strobe
Beam Distance	375 yd / 343 m
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP54
Structure	6000 Series Aluminum, Type II Anodize Finish
Length / Weight	9.0" / 1.2 lbs



**Includes:** (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Lanyard, Charger

**M12™ Spot Light**

2353-20 Tool-Only

**Specifications:**

Lumens	750 / 400 / 750
Modes	High, Low, Strobe
Beam Distance	700 yd / 640 m
Water & Dust Rating	IP54
Length / Weight	6.1" / 1.4 lbs



Battery and Charger Sold Separately

**Includes:** Lanyard

**M12™ Lantern/Flood Light**

2362-20 Tool-Only

**Specifications:**

Lumens	400 / 200 / 40 / 400
Modes	High, Medium, Low, Strobe
Beam Pattern	Adjustable 180° – 360°
Water & Dust Rating	IP54
Hands-Free	2 Hooks for Hanging
USB Charger	2.1A USB Charging Port for External Devices
Length / Weight	10.5" / 1.0 lb



Battery and Charger Sold Separately



**M12™ ROVER™ Mounting Flood Light**

2364-20 Tool-Only

**Specifications:**

Lumens	1,000 / 400 / 200
Modes	High, Medium, Low
Hands Free	Integrated Magnet, Spring Loaded Clamp
Water & Dust Rating	IP54
Length / Weight	7.5" / 2.2 lbs



Battery and Charger Sold Separately

**M12™ Underhood Light Kit**

2125-21XC (2125-20 Tool-Only)

**Specifications:**

Lumens	1,350 / 600
Modes	High, Low
Hooks	FINISHGUARD™ to Resist Wear & Provide Lasting Protection
Length / Weight	48" Collapsed, 78" Fully Extended / 2.2 lbs



**Includes:** (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, Charger

**M12™ Stick Light**

2351-20 Tool-Only

**Specifications:**

Lumens	220
Hands-Free	Multi-Position Stainless Steel Hook
Water & Dust Rating	IP54
Length / Weight	9.3" / 0.6 lbs



Battery and Charger Sold Separately

**Related Accessory:**  
49-24-2351 M12™ Stick Light Magnet  
Holds light to metal surfaces for hands-free use

**M12™ Work Light**

49-24-0146 Tool-Only

**Specifications:**

Lumens	100
Hands-Free	Integrated Magnet
Head Rotation	90°



Battery and Charger Sold Separately



**M12™ Heated TOUGHSHELL™ Jacket Kit**

Black 202B-21 (S – 3X)\*  
202B-20 Jacket-Only

Red 202R-21 (S – 3X)\*  
202R-20 Jacket-Only

**Specifications:**

Heat Zones	3 (Chest, Back, Pockets)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	TOUGHSHELL™ Stretch Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes



**Includes:** (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source

**M12™ Heated QUIETSHELL Jacket Kit**

Camo 222C-21 (S – 3X)\*  
222C-20 Jacket-Only

**Specifications:**

Heat Zones	3 (Chest, Back, Pockets)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	QUIETSHELL™ Stretch Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes



**Includes:** (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source

**M12™ Heated AXIS™ Jacket Kit**

Black 203B-21 (S – 3X)\*  
203B-20 Jacket-Only

**Specifications:**

Heat Zones	3 (Chest, Back, Shoulders)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	AXIS™ Ripstop Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes



**Includes:** (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source

**M12™ Women's Heated AXIS™ Jacket Kit**

Black 233B-21 (S – 2X)\*  
233B-20 Jacket-Only

**Specifications:**

Heat Zones	3 (Chest, Back, Shoulders)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	AXIS™ Ripstop Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes



**Includes:** (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source



**M12™ Heated Hoodie Kit**

Black 302B-21 (S – 3X)\*  
302B-20 Hoodie-Only

Gray 302G-21 (S – 3X)\*  
302G-20 Hoodie-Only

Red 302R-21 (S – 3X)\*  
302R-20 Hoodie-Only

**Specifications:**

Heat Zones	2 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Wind Resistant	Yes
Washer / Dryer Safe	Yes



**Includes:** (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, M12™ Battery Holder, Charger

\*MODEL NUMBER EXAMPLE  
202B-21S = M12™ Heated TOUGHSHELL™ Black Jacket Kit in Small