

M18™ RADIUS™ LED Compact Site Light

2145-20

Specifications:

Lumens	4,400 / 2,100 / 1,000
Modes	High, Medium, Low
Moisture Resistance	IP54
Powered By	M18™ or Corded
Hands Free	Self-Centering Metal Hook
Daisy Chain Compatible	Yes
Weight	10.6 lbs



Battery and Charger Sold Separately

Includes: Security Cable

POWERED BY



M18™ LED Stick Light

2352-20

Specifications:

Lumens	300 / 150
Modes	High, Low
Moisture Resistance	IP54
Pivoting Head	45°
Hands Free	2 Stainless Steel Hooks
Length	11-5/8"
Weight	1.1 lbs



Battery and Charger Sold Separately



M18™ ROVER™ LED Dual Power Flood Light

2360-20

Specifications:

Lumens	3,000 / 1,500 / 650
Modes	High, Medium, Low
Powered By	M18™ or Corded
Hands Free	(3) Keyholes for Hanging
Length	9"
Weight	6.4 lbs



Battery and Charger Sold Separately

POWERED BY



M18™ Lantern/Flood Light

2363-20

Specifications:

Lumens	700 / 350 / 70 / 700
Modes	High, Medium, Low, Strobe
Beam Pattern	Adjustable 180° – 360°
Moisture Resistance	IPX4
Hands Free	2 Stainless Steel Hooks
USB Charger	2.1A USB Charging Port
Length	11-1/2"
Weight	1.2 lbs



Battery and Charger Sold Separately



M18™ ROVER™ LED Flood Light

2361-20

Specifications:

Lumens	1,500 / 780
Modes	High, Low
Moisture Resistance	IP54
Hands-Free	(1) Keyhole for Hanging, (1) EMT Hanger
Length	8-3/4"
Weight	3.4 lbs



Battery and Charger Sold Separately



M18™ LED Search Light

2354-21 (2354-20 Tool-Only)

Specifications:

Lumens	1,250 / 1,200 / 600 / 1,200
Modes	Spot/Flood, Flood, Spot, Strobe
Beam Distance	730 yd / 667.5 m
Moisture Resistance	IP54
Head Rotation	198°
Length	11-1/2"
Weight	3.1 lbs



Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger, Shoulder Strap



M18™ LED Work Light

2735-20

Specifications:

Lumens	100
Hands Free	Integrated Hook
Head Rotation	90°



Battery and Charger Sold Separately



M18™ LED Utility Bucket Light

2122-22HD, 2122-21HD (2122-20 Tool-Only)

Specifications:

Lumens	2,500 / 2,200 / 800
Modes	Flood, Spot/Flood, Spot
Hands Free	Patented Spring Loaded Bucket Clamp
Moisture Resistance	IP56
Length	13-3/4"
Weight	10.5 lbs



Includes: 2122-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Storage Bag; 2122-21HD Includes (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack



M18 FUEL™ String Trimmer Kit

2725-21HD (2725-20 Tool-Only)

Specifications:

Cutting Swath	14" – 16"
Line Diameter	.080" / .095"
RPM	0 – 4,600 / 0 – 5,800
Trigger	Variable Speed
Feed System	Bump Feed
Length	73-3/5"
Weight	12.3 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger

M18 FUEL™ Hedge Trimmer Kit

2726-21HD (2726-20 Tool-Only)

Specifications:

Blade Length	24"
Cut Capacity	3/4"
SPM	3,400
Gear Case	All-Metal
Length	45-3/4"
Weight	10.9 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger

M18 FUEL™ Blower Kit

2728-21HD (2728-20 Tool-Only)

Specifications:

Max Air Volume	450 CFM
Max Air Speed	100 MPH
Noise Rating (db)	63 (ANSI B175)
Cruise Control	Yes
Length	38-1/2"
Weight	8.1 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger

M18™ Compact Blower

0884-20

Specifications:

Max Air Volume	100 CFM
Max Air Speed	160 MPH
Switch	3-Speed Electronic
Length	20-1/2"
Weight	2.6 lbs



Battery and Charger Sold Separately

Includes: Flexible Nozzle, 9" Extension, Universal Inflator/Deflator

M18™ Compact Vacuum

0882-20

Specifications:

Air Volume	40 CFM
Inlet Diameter	1-1/4"
Canister Volume	36 oz
Filter	HEPA
Weight	4.3 lbs



Battery and Charger Sold Separately

Includes: 4' Hose, (2) Extension Tools, Crevice Tool, Floor Tool, Removable HEPA Filter

Related Accessory: 49-90-1951 Filter

M18™ Wet/Dry Vacuum

0880-20

Specifications:

Material	Wet/Dry
Capacity	2 gal
Air Volume	45 CFM
Suction (H ₂ O)	32"
Washable Filter	Yes; HEPA
Compatibility	All MILWAUKEE® 18V Slide-On Batteries (LITHIUM-ION or NiCd)



Battery and Charger Sold Separately

Includes: HEPA Filter, Flexible Hose, Filter Assembly, Crevice Tool, Wide Utility Nozzle

Related Accessory: 49-90-1900 Filter

M18™ Jobsite Fan

0886-20

Specifications:

Max Air Flow	284 CFMs (18 MPH)
RPM (3 Settings)	1,370 / 1,900 / 2,350
Length	10-3/10"
Weight	5.2 lbs



Battery and Charger Sold Separately

Includes: AC Adapter

M18™ Radio Charger

2792-20

Specifications:

Modes	AM, FM, AUX, Bluetooth®
Battery Charger	Charges all M18™ Batteries
Bluetooth® Antenna	100 ft Range
USB Charging Port	2.1 Amps
Powered By	All M18™ Batteries, 120V AC



Battery Sold Separately

Includes: 16" Auxiliary Input Cord, (2) AAA Batteries (For Memory Backup)

CHARGES

