

M18™ FORCE LOGIC™ Cable Cutter Kit w/ 750 MCM Cu Jaws

2672-21

Specifications:

Capacity	750 MCM Cu, 1,000 MCM Al
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Length	14"

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, 750 MCM Cable Cutter Jaw, Allen Wrench, Multi-Voltage Charger, Carrying Case



M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit w/ Wireless Remote

2776R-21



Specifications:

Hydraulic Output Force	9 Tons
Cut Capacity	1500 MCM Cu 15KV
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	20-4/5"
Weight	15.75 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Remote, Carabiner, M18™ AC/DC Wall and Vehicle Charger, Utility Bag

Related Accessories:

49-16-2774 3" Underground Replacement Blades



M18™ FORCE LOGIC™ 10 Ton Knockout Tool Kit

2676-23, 2676-22 (2676-20 No Punches or Dies)

Specifications:

Mild Steel Capacity	6" in 12 Gauge
Stainless Steel Capacity	6" in 14 Gauge
Output Force	10 Ton
Quick-Connect Draw Stud	Yes
Weight	7.1 lbs
Height	5-1/2"

Includes: 2676-23 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, EXACT™ 1/2" – 4" Conduit Punches and Dies, (3) Draw Studs, Quick Connect Alignment System, Multi-Voltage Charger, Carrying Case; 2676-22 Includes 1/2" – 2" EXACT™ Conduit Punches and Dies; 2676-20 Includes No Punches or Dies



M18™ FORCE LOGIC™ Press Tool Kit

2773-22 (2773-20 No Jaw Kit)

Specifications:

Capacity	1/2" – 4" (Varies by Material)
Weight	6.5 lbs
Length	14-1/10"
Calibration Interval	50,000 Cycles (LED Indicator)
Approximate Cycle Time	3.7 Seconds
Press Force	7,200 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, (6) Jaws (1/2", 3/4", 1", 1-1/4", 1-1/2", 2"), Multi-Voltage Charger, Carrying Case; 2773-20 Includes No Jaws



M18™ FORCE LOGIC™ Cable Cutter Kit w/ 477 ACSR Jaws

2672-21S

Specifications:

Capacity	477 HEN ACSR
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Length	14"

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, 477 ACSR Cutting Jaw, Carabiner, Allen Wrench, AC/DC Wall and Vehicle Charger, Bucket Bag



M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit

2776-21



Specifications:

Hydraulic Output Force	9 Tons
Cut Capacity	1500 MCM Cu 15KV
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	20-4/5"
Weight	15.75 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Carabiner, M18™ AC/DC Wall and Vehicle Charger, Utility Bag

Related Accessories:

49-16-2774 3" Underground Replacement Blades



M18™ FORCE LOGIC™ Knockout Accessories

Compatible with 2677-20 and 2676-20

EXACT™ Accessory Kits

49-16-2692 1/2" – 1-1/4" Knockout Set;
49-16-2693 1/2" – 2" Knockout Set;
49-16-2694 1/2" – 2" Hand Ratchet Knockout Set;
49-16-2695 2-1/2" – 4" Knockout Set

EXACT™ Punches and Dies

49-16-2660* 1/2" Die;
49-16-2660S 1/2" Die;
49-16-2661* 1/2" Punch;
49-16-2661S 1/2" Punch;
49-16-2662 3/4" Die;
49-16-2663 3/4" Punch;
49-16-2664 1" Die;
49-16-2665 1" Punch;
49-16-2666 1-1/4" Die;
49-16-2667 1-1/4" Punch;
49-16-2668 1-1/2" Die;
49-16-2669 1-1/2" Punch;
49-16-2670 2" Die;
49-16-2671 2" Punch;
49-16-2672 2-1/2" Die;
49-16-2673 2-1/2" Punch;
49-16-2674 3" Die;
49-16-2675 3" Punch;
49-16-2676 3-1/2" Die;
49-16-2677 3-1/2" Punch;
49-16-2678 4" Die;
49-16-2679 4" Punch;
49-16-2686 5" Die;
49-16-2687 5" Punch;
49-16-2688 6" Die;
49-16-2689 6" Punch

*These items are intended only for Mild Steel.

EXACT™ Sink Punches & Dies

49-16-2705 7/8" Sink Die;
49-16-2706 7/8" Sink Punch;
49-16-2700 1-3/8" Sink Die;
49-16-2701 1-3/8" Sink Punch

Draw Studs

49-16-2621 3/8" Ball Bearing Draw Stud;
49-16-2622 3/4" Ball Bearing Draw Stud;
49-16-2680 7/16" Draw Stud;
49-16-2681 3/4" Draw Stud;
49-16-2682 1-1/8" Draw Stud;
49-16-2707 1-1/8" Long Draw Stud

Adapters

49-16-2684 3/8" Adapter for EXACT™ 2-1/2" – 4" Dies to 3/4" Draw Studs;
49-16-2685 Adapter for M18™ FORCE LOGIC™ Knockout Tool to other major brands of punches and dies

M18™ FORCE LOGIC™ Long Throw Press Tool Kit

2673-22L (2673-20L No Jaw Kit)

Specifications:

Capacity	1/2" – 4" CU, 1/2" – 2" SS
Weight	10.1 lbs
Length	20-1/8"
Calibration Interval	40,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds, 10 Seconds at Full Stroke
Press Force	7,200 lbs

Includes: 2673-22L (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (3) Jaws (1/2", 3/4", 1"), Multi-Voltage Charger, Carrying Case; 2673-20L Includes No Jaws



M18™ FORCE LOGIC™ Cable Cutter Accessories

Compatible with 2672-21 and 2672-21S

Cutter Jaws

49-16-2772 M18™ Cu/Al Cutting Jaw;
49-16-2773 M18™ ACSR Cutting Jaw

Cutter Replacement Blades

48-44-0411 Replacement Copper Blades;
48-44-0412 Replacement Steel Blades

M18™ FORCE LOGIC™ 1590 ACSR Cutter Kit

2777-21



Specifications:

Hydraulic Output Force	9 Tons
Cut Capacity	Up to 1590 Falcon ACSR
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16-3/4"
Weight	11.75 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Carabiner, Side Handle, AC/DC Wall and Vehicle Charger, Utility Bag

Related Accessories:

49-16-2775 1590 ACSR Replacement Blades



M18™ FORCE LOGIC™ 6 Ton Knockout Tool Kit

2677-21 (2677-20 No Punches or Dies)

Specifications:

Mild Steel Capacity	4" in 14 Gauge
Stainless Steel Capacity	2" in 14 Gauge
Output Force	6 Ton
Quick-Connect Draw Stud	Yes
Weight	4.3 lbs
Height	4-1/2"

Includes: 2677-21 (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, EXACT™ 1/2" – 2" Conduit Punches and Dies, (2) Draw Studs, Quick Connect Alignment System, Multi-Voltage Charger, Carrying Case; 2677-20 Includes No Punches or Dies

