

## Multi-function I/O Port to Contact Closure/Relay Converter



# KD-CCXR200

Converts MCP35™ Multi-function I/O Port to Contact Closure/Relay

### Key Features

- › **Compatible with:** KD-MC1000, KD-MC2500 and Digital IQ Series™ Matrix Switchers
- › **Multifunction 3.5mm based Compass Control® Port – MCP35™:** supports following seven features:
  - › 1. IR output
  - › 2. IR Input
  - › 3. RS232 bi-directional
  - › 4. Voltage sensor
  - › 5. Voltage trigger
  - › 6. PCM audio sensor
  - › 7. Composite Video sensor
- › **Converts:** Any I/O Multifunction Compass® Control Port (MCP35™) to Contact Closure/Relay when set to Output Voltage Trigger Mode
- › **Contact Functionality:** Contact Normally Open, if 5V applied – Contact Closed.
- › **3.5mm mono input connection:** Use a male-to-male 3.5mm mono cable from KD-MC1000, KD-MC2500 and Digital IQ Series™ Matrix Switchers
- › **One Contact Closure/Relay Output**
- › **Contact Closure Maximum Rating:** 250VAC/5A, 30VDC/5A
- › **Maximum Distances:**
  - › 3.5mm mono cable: 10 feet
  - › Contact Closure/Relay Output with one twisted pair of CAT5e/6 cable: 100 feet
- › **No external power required**



### Usage Examples

