

CSA 200A 3P 600V 3W FUSED HD TYPE 3R



Installation location	OUTDOOR
Manner of function of the actuating element	SINGLE THROW
Mechanical service life (switching cycles) typical	8000
Mounting type	2 OR 3 POINT MOUNTING HOLES
Number of poles	3

### Electricity

Ampacity	200 A
Supply voltage frequency rated value 50/60 Hz	Yes
Voltage between phase and phase rated value	600 V

### Switching capacity

Switching capacity active power	3 W
---------------------------------	-----

### Environmental conditions

Ambient temperature during operation maximum	120 °C
Ambient temperature during operation minimum	-20 °C

### Model

Product brand name	SIEMENS
Product type designation	ENCLOSED/SAFETY SWITCH

Mechanical Design	
Design of the housing	TYPE 3R
Material	304SS
General product approval	
Certificate of suitability	CSA
<b>last modified:</b>	05/28/2019