















# 4" LOW VOLTAGE TRIM SERIES LENSED

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

Trim Series	Dimensions	Catalog No.	Housing/Lamp Compatibility
 <p><b>Downlight/ Adjustable Lensed Trim</b></p>	 <p>Adjustment: 35° Vertical</p> 	<p><b>441W-ABZ</b> - Perimeter Frosted Lens, Classic Aged Bronze Trim <b>441W-SC</b> - Perimeter Frosted Lens, Satin Chrome Trim <b>441W-WH</b> - Perimeter Frosted Lens, White Trim</p>	<p>IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16 TC47/TC47V: 50W MR16 APT44: 50W MR16</p>
 <p><b>Beveled Lensed</b></p>	 <p>Adjustment: 30° Vertical</p> 	<p><b>4402-ABZ</b> - Regressed Perimeter Frosted Glass Lens, Classic Aged Bronze Trim <b>4402-SC</b> - Regressed Perimeter Frosted Glass Lens, Satin Chrome Trim <b>4402-WH</b> - Regressed Perimeter Frosted Glass Lens, White Trim</p>	<p>IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16</p>
 <p><b>Beveled Dome Lensed</b></p>	 	<p><b>4401-ABZ</b> - Frosted Glass Lens, Classic Aged Bronze Trim <b>4401-SC</b> - Frosted Glass Lens, Satin Chrome Trim <b>4401-WH</b> - Frosted Glass Lens, White Trim</p>	<p>IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16</p>
 <p><b>Frosted Glass</b></p>	 	<p><b>4481CLEAR</b> - Perimeter Frosted Clear Glass</p>	<p>IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16</p>

