D1.3.5

JUNO

Project:

Fixture Type:

Location:

Contact/Phone:

TRAC-MASTER® Avant Garde **OPEN BACK SPOTLIGHTS** T196, T696, T362, T363 and T368

PRODUCT DESCRIPTION

The clean, functional lines of the open back allows maximum adjustability. Open Back Spotlights relamp from back and have floating socket mount and on/off switch. The minimum profile with stylized yoke design is ideal for retail and commercial applications.

Construction Die-formed steel.

Aiming 90° vertical aiming capability and 358° rotation.

Labels UL listed, CSA certified.

Product specifications subject to change without notice.



Low Voltage MR16

Lampholder Ceramic bi-pin.


Transformer T537 or T538 12V solid state electronic transformer with on/off switch • Dimmable • Must be ordered separately


• Refer to specification sheet D1.2.1.

Catalog Number	Finish	Lamp	
T196WH	White	20-50W MR16	
T196BL	Black	20-50W MR16	
T196SC	Satin Chrome	20-50W MR16	

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T551-5	Color Filters	T557	Prismatic Spread Lens	T559	Linear Spread Lens
T5501-18	Dichroic Filters	T5520	Diffusion Lens	T5521	Uniformity Lens
T5522	UV Filter	T5559BL	Hexcell Louver		
See specification	n sheet D1 2 2 for details	:			





Low Voltage MR16


Lampholder Ceramic bi-pin.


Transformer T537 or T538 12V solid state electronic transformer with on/off switch • Dimmable • Must be ordered separately • Refer to specification sheet D1.2.1.

Catalog Number	Finish	Lamp	
T696WH	White	20-75W MR16	
T696BL	Black	20-75W MR16	

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T551-5	Color Filters	T557	Prismatic Spread Lens	T559	Linear Spread Lens
T5501-18	Dichroic Filters	T5520	Diffusion Lens	T5521	Uniformity Lens
T5522	UV Filter	T5559BL	Hexcell Louver		
See specification	n sheet D1.2.2 for detail	δ.			







D1.3.5

TRAC-MASTER® Avant Garde **OPEN BACK SPOTLIGHTS**


T196, T696 T362, T363 and T368

Line Voltage PAR20

Lampholder Medium base porcelain with nickel plated copper screw shell.

Adapter Copper alloy contacts provide precise spring action - no arcing and will not take a set • True, positive electrical ground • On/off switch included · Patented embossed polarity arrows on bottom of adapter · Spring-loaded positive latch with embossed polarity arrows secures trac light to trac • "Pull-up" contact to up position for two-circuit application.


Catalog Number	Finish	Lamp	
T362WH	White	35-50W PAR20	
T362BL	Black	35-50W PAR20	
T362SC	Satin Chrome	35-50W PAR20	



Line Voltage PAR30

Lampholder Medium base porcelain with nickel plated copper screw shell. Adapter Refer to T362.

Catalog Number	Finish	Lamp	
T363WH	White	35-75W PAR30	
T363BL	Black	35-75W PAR30	
T363SC	Satin Chrome	35-75W PAR30	
T363NA	Natural	35-75W PAR30	



Line Voltage PAR38


Lampholder Medium base porcelain with nickel plated copper screw shell. Adapter Refer to T362.

Catalog Number	Finish	Lamp	
T368WH	White	45-150W PAR38	
T368BL	Black	45-150W PAR38	
T368SC	Satin Chrome	45-150W PAR38	
T368NA	Natural	45-150W PAR38	

ACCESSODIES

ACCESSO	VRIES				
Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T571-6	Color Filters	T579BL	Cube Cell Louver	T5721	Uniformity Lens
T5722	UV Filter	T5777	Prismatic Spread Lens	T5778	Linear Spread Lens
T5718	Color Correction Filter				

See specification sheet D1.2.2 for details.





1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925 Juno Liefino Group 220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064 by schneider Electric Visit us at www.junolightinggroup.com Printed in U.S.A. ©2010 Juno Lighting, LLC.