

# **ECONOMY RECESSED LIGHTING**







# Viewing economy recessed downlighting in a different light

Take a new view on economy lighting with VuLite from Juno Lighting Group. VuLite is an economic alternative for recessed lighting offering a selection of 4", 5" and 6" downlights for use in residential and light commercial applications. The line includes a range of popular trim selections including baffles, cones, adjustables and lensed, providing choices to meet the needs of various lighting applications. Economy does not mean sacrificing the quality and standards you have come to expect from Juno Lighting Group. You can buy and install VuLite products with total confidence knowing that all products are designed and tested to meet UL requirements and are backed by the leader in residential recessed lighting.

# **VuLite Product Offering**

## 4" Housings and Trims

#### Line Voltage Housings



#### Low Voltage Housings



#### 4" Trims





# 5" Housings and Trims



#### **Line Voltage Housings**



5" Trims



# 6" Housings and Trims

#### **Line Voltage Housings**





# **ULITE** 4" Line Voltage Housings and Trims

#### IC Housing

#### V4ICW

4" IC New Construction Energy efficient double wall

housing. May be covered with insulation.

Dimensions:

12"L x 13-3/8"W x 6"H

Ceiling Cutout: 4-1/2" Dia.





### TC Housings

#### V4TCW

4" TC New Construction

Requires 3" spacing from insulation.

12-1/8"L x 13-3/8"W x 5-1/2"H

Ceiling Cutout: 4-1/2" Dia.

#### V4TCRW

4" TC Remodel

Requires 3" spacing from insulation.

Dimensions: 12"L x 4-1/4"W x 5-1/2"H

Ceiling Cutout: 4-3/8" Dia.

Accessories: VALG4 Airloc® gasket kit for V4IC housing when an Airloc® trim is not being used.

**G2405** Set of (4) T-bar clips for installation in suspended ceilings.

#### 4" Compatible Trims - Line Voltage

#### **Baffle**

V4034W-WH: White V4034B-WH: Black

Aperture: 3-7/8" Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type

V4TCW, V4TCRW: 50W PAR20, 50W R20

Juno Compatible Housing: Lamp Wattage/Type

IC1P, TC1, TC1R: 50W PAR20, 50W R20 IC1: 50W PAR20, 30W R20

V4ICW: 50W PAR20, 30W R20

V4017C-WH: Clear

Aperture: 3-7/8" Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type

V4ICW, V4TCW, V4TCRW: 50W PAR20, 50W R20 Juno Compatible Housing: Lamp Wattage/Type IC1, IC1P, TC1, TC1R: 50W PAR20, 50W R20

#### **Gimbal Ring**

V4010-WH: White V4010-BN: Brushed Nickel

Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type V4ICW, V4TCW, V4TCRW: 50W PAR20

Juno Compatible Housing: Lamp Wattage/Type

IC1P, TC1, TC1R: 50W PAR20



V4018-WH: White

Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type

V4ICW, V4TCW, V4TCRW: 60W PAR16, 40W R16 Juno Compatible Housing: Lamp Wattage/Type IC1, IC1P, TC1, TC1R: 60W PAR16, 40W R16



#### Stippled Opal Lens Shower with Reflector

V4012-WH: White

Outer Diameter: 5"



V4TCW, V4TCRW: 50W PAR20, 50W R20

Juno Compatible Housing: Lamp Wattage/Type (Remove reflector when using Juno IC1 housing)

IC1: 35W PAR20, 30W R20 IC1P: 50W PAR20, 30W R20 TC1, TC1R: 50W PAR20, 50W R20













## 4" Low Voltage Housings and Trims



#### IC Housing

#### V4ICLVW

4" IC Low Voltage New Construction

50W Energy efficient double wall housing includes 50VA, 12V thermally protected magnetic transformer. May be covered with insulation.

Dimensions:

18-1/2"L x 13-3/8"W x 7-5/8"H

Ceiling Cutout: 4-1/2" Dia.

### TC Housings

#### V4TCLVW

AIR-LOC

4" TC Low Voltage New Construction

50W Housing includes 50VA, 12V thermally protected magnetic transformer. Requires 3" spacing from insulation.

12-1/8"L x 13-3/8"W x 5-1/2"H

Ceiling Cutout: 4-1/2" Dia.

4" TC Low Voltage Remodel 50W Housing includes 50VA, 12V magnetic transformer. Requires 3" spacing

Ceiling Cutout: 4-3/8" Dia.




#### V4TCRLVW

from insulation.

Dimensions:

14-1/2"L x 4-1/4"W x 5-1/2"H

4" Compatible Trims - Low Voltage



in suspended ceilings.

Accessory: G2405 Set of (4) T-bar clips for installation

V4044W-WH: White V4044B-WH: Black

Aperture: 3-1/2" Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type

V4ICLVW, V4TCLVW, V4TCRLVW: 50W MR16 Juno Compatible Housing: Lamp Wattage/Type IC44N, TC44, TC44V, TC44R, TC47, TC47V: 50W

Eyeball with Baffle V4048-WH: White

Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type

V4ICLVW, V4TCLVW, V4TCRLVW: 50W MR16 Juno Compatible Housing: Lamp Wattage/Type

IC44N, TC44, TC44V, TC44R, TC47, TC47V: 50W MR16

Cone with Regressed Gimbal Ring

V4047C-WH: Clear

Aperture: 3-1/2" Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type V4ICLVW, V4TCLVW, V4TCRLVW: 50W MR16 Juno Compatible Housing: Lamp Wattage/Type

IC44N, TC44, TC44V, TC44R, TC47, TC47V: 50W MR16

Stippled Opal Lens Shower

V4041-WH: White

Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type V4ICLVW, V4TCLVW, V4TCRLVW: 50W MR16

Juno Compatible Housing/Lamp:

IC44N, TC44, TC44V, TC44R, TC47, TC47V: 50W MR16

**Gimbal Ring** 

V4040-WH: White V4040-BN: Brushed Nickel

Outer Diameter: 5"

VuLite Housing: Lamp Wattage/Type V4ICLVW, V4TCLVW, V4TCRLVW: 50W MR16

Juno Compatible Housing: Lamp Wattage/Type IC44N, TC44, TC44V, TC44R, TC47, TC47V: 50W MR16











# 5" Line Voltage Housings and Trims

### IC Housings

#### V5ICW

#### 5" IC New Construction

Energy efficient housing. May be covered with insulation.

**Dimensions:** 

11-7/8"L x 13-3/8"W x 7-1/2"H

Ceiling Cutout: 5-5/8" Dia.



#### V5ICRW

#### 5" IC Remodel

Energy efficient housing. May be covered with insulation.

Dimensions:

14-3/8"L x 6-3/4"W x 7-1/2"H

Ceiling Cutout: 5-1/2" Dia.



## TC Housings

#### V5TCW

#### 5" TC New Construction

Requires 3" spacing from insulation.

11-7/8"L x 13-3/8"W x 7-1/2"H

Ceiling Cutout: 5-5/8" Dia.



#### **V5TCRW**

#### 5" TC Remodel

Requires 3" spacing from insulation.

Dimensions:

12-1/2"L x 5-7/8"W x 7-1/2"H

Ceiling Cutout: 5-1/2" Dia.



Accessories: VALG4 Airloc® gasket kit for V4IC housing when an Airloc® trim is not being used.

AIR-LOC

**G2405** Set of (4) T-bar clips for installation in suspended ceilings.

### 5" Compatible Trims

#### **Baffle**

V2015W-WH: White V2015B-WH: Black

Aperture: 4-3/4"

Outer Diameter: 6-1/4"





V2016C-WH: Clear V2016W-WH: White

Aperture: 4-3/4"

Outer Diameter: 6-1/4"





#### VuLite Housing: Lamp Wattage/Type

V5ICW, V5ICRW: 65W BR30, 75W PAR30L,

75W PAR30 w/socket extender, 50W PAR30 (black only)

V5TCW, V5TCRW: 85W BR30, 75W PAR30L,

40W A19 (white only), 75W PAR30 (black only or use socket

extender with white)

#### Juno Compatible Housing: Lamp Wattage/Type

IC20, IC20R: 40W A19, 65W BR30, 75W PAR30L,

75W PAR30 w/socket extender

IC20N: 65W BR30

TC20, TC20R: 60W A19, 85W BR30, 75W PAR30L,

75W PAR30 w/socket extender

# VuLite Housing: Lamp

Wattage/Type

V5ICW, V5ICRW: 65W BR30, 75W PAR30L,

75W PAR30 w/socket extender

V5TCW, V5TCRW: 85W BR30, 75W PAR30L,

75W PAR30 w/socket extender, 60W A19 (clear only),

40W A19 (white only)

#### Juno Compatible Housing: Lamp Wattage/Type

IC20, IC20R: 40W A19, 65W BR30, 75W PAR30L,

75W PAR30 w/socket extender

IC20N: 65W BR30

TC20, TC20R: 60W A19, 85W BR30, 75W PAR30L,

75W PAR30 w/socket extender



# 5" Line Voltage Housings and Trims



#### 5" Compatible Trims (continued)

R/PAR20 Eyeball V2029-WH: White

Outer Diameter: 6-1/4"



VuLite Housing: Lamp Wattage/Type **V5ICW, V5ICRW:** 50W R20, 50W PAR20 V5TCW, V5TCRW: 50W R20, 50W PAR20 Juno Compatible Housing: Lamp Wattage/Type

IC20, IC20N, IC20R, TC20, TC20R: 50W PAR20, 50W R20

Flat Lens Shower with Reflector V2010-WH: White

Outer Diameter: 6-1/2"





VuLite Housing: Lamp Wattage/Type V5ICW, V5ICRW: 35W PAR30L

V5TCW, V5TCRW: 75W PAR30L, 90W A19 Juno Compatible Housing: Lamp Wattage/Type

IC20, IC20R: 35W PAR30L & 40W A19

**IC20N**: 35W PAR30L

TC20, TC20R: 75W PAR30L & 90W A19

PAR30 Eyeball V2030-WH: White

Outer Diameter: 6-1/2"



VuLite Housing: Lamp Wattage/Type V5ICW, V5ICRW: 75W PAR30 V5TCW, V5TCRW: 75W PAR30

Juno Compatible Housing: Lamp Wattage/Type IC20, IC20N, IC20R, TC20, TC20R: 75W PAR30



# **Vulite** 6" Line Voltage Housings and Trims

## **IC Housings**

V6ICW 6" IC New Construction V6ICNW 6" IC New Construction with Floating Socket

Energy efficient housing. May be covered with insulation.

Dimensions:

13-3/4"L x 13-3/8"W x 7-3/8"H Ceiling Cutout: 6-1/2" Dia.



#### V6ICRW

#### 6" IC Remodel

Energy efficient housing. May be covered with insulation.

Dimensions:

13-3/4"L x 6-3/4"W x 7-3/8"H

Ceiling Cutout: 6-1/4" Dia.

AIR-LOC

### TC Housings

#### V6TCW

#### 6" TC New Construction

Requires 3" spacing from insulation.

13-3/4"L x 13-3/8"W x 7-3/8"H

Ceiling Cutout: 6-1/2" Dia.

#### V6TCRW

#### 6" TC Remodel

Requires 3" spacing from insulation.

Dimensions:

13-3/4"L x 6-3/4"W x 7-3/8"H

Ceiling Cutout: 6-1/4" Dia.



Accessories: VALG4 Airloc® gasket kit for V4IC housing when an Airloc® trim is not being used.

G2405 Set of (4) T-bar clips for installation in suspended ceilings.

### 6" Compatible Trims

#### **Conical Baffle**

V3024W-WH: White V3024B-WH: Black

Aperture: 5-3/4"

Outer Diameter: 7-3/4"



#### VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICRW: 50W PAR30, 75W PAR30L, 65W BR30 V6TCW, V6TCRW: 75W PAR30/PAR30L, 65W BR30,

120W BR40

#### Juno Compatible Housing: Lamp Wattage/Type

IC22, IC22R: 50W PAR30, 75W PAR30L, 65W BR30 IC2, TC2, TC2R: 75W PAR30 w/socket extender,

75W PAR30L, 65W BR30

#### Straight Baffle

V3025W-WH: White V3025B-WH: Black

Aperture: 5-3/4" Outer Diameter: 7-3/4"



#### VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICRW: 50W PAR30/PAR30L, 75W PAR38 V6TCW, V6TCRW: 75W PAR30/PAR30L, 65W BR30, 120W BR40,120W PAR38

Juno Compatible Housing: Lamp Wattage/Type

IC22, IC22R: 75W PAR30/PAR30L, 65W BR30, 75W PAR38 IC2: 75W PAR30 w/socket extender, 75W PAR30L, 65W BR30, 90W PAR38, 100W BR40

TC2, TC2R: 75W PAR30 w/socket extender, 75W PAR30L,

65W BR30, 150W PAR38, 120W BR40

#### Full Baffle

V3034W-WH: White V3034B-WH: Black

V3034TW-WH: White w/Torsion Springs V3034TB-WH: Black w/Torsion Springs

Aperture: 5-3/4" Outer Diameter: 7-5/8"



V6ICW, V6ICNW, V6ICRW: 40W A19\*, 75W PAR30/PAR30L,

65W BR30, 90W BR40, 90W PAR38\*

V6TCW, V6TCRW: 60W A19\*, 75W PAR30/PAR30L,

85W BR30, 120W BR40, 150W PAR38\* \* No A19 listing and 75W PAR38 max. for the V3034B Series

#### Juno Compatible Housing: Lamp Wattage/Type

IC22, IC22R, IC23: 40W A19, 75W PAR30/PAR30L, 65W BR30, 90W BR40, 90W PAR38

IC2: 60W A19, 75W PAR30/PAR30L, 85W BR30, 100W PAR38, 120W BR40

TC2, TC2R: 60W A19, 75W PAR30/PAR30L, 85W BR30.

150W PAR38, 120W BR40 ICPL6 Series: 32W max. CFL† PL6 Series: 42W max CFL†

†Note: For best performance, 26W is recommended.

Patent Pending

#### Clear Cone

V3027C-WH: Clear

Aperture: 5-3/4" Outer Diameter: 7-3/4"



#### VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICRW: 50W PAR30, 75W PAR30L, 65W BR30 V6TCW, V6TCRW: 75W PAR30/PAR30L, 65W BR30, 90W BR40

Juno Compatible Housing: Lamp Wattage/Type

IC2, IC22, IC22R: 50W PAR30, 75W PAR30L, 65W BR30

TC2, TC2R: 75W PAR30/PAR30L, 65W BR30





## 6" Line Voltage Housings and Trims



#### **6" Compatible Trims** (continued)

**Full Cone** 

V3037W-WH: White

V3037TW-WH: White w/ Torsion Springs

Aperture: 5-3/4" Outer Diameter: 7-5/8"

VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICNW, V6ICRW: 40W A19, 75W PAR30/PAR30L,

65W BR30, 75W BR40, 90W PAR38

V6TCW, V6TCRW: 60W A19, 75W PAR30/PAR30L, 85W BR30,

120W BR40, 150W PAR38

Juno Compatible Housing: Lamp Wattage/Type

IC22, IC22R, IC23: 40W A19, 75W PAR30/PAR30L, 65W BR30,

90W BR40, 90W PAR38

IC2: 60W A19, 75W PAR30/PAR30L, 85W BR30, 100W PAR38

TC2, TC2R: 60W A19, 75W PAR30/PAR30L, 85W BR30,

120W BR40, 150W PAR38 ICPL6 Series: 32W max. CFL† PL6 Series: 42W max CFL†

†Note: For best performance, 26W is recommended.

Patent Pending

**Stippled Opal Lens Shower** with Reflector

V3040N-PW: Plastic White

Outer Diameter: 8"

VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICNW, V6ICRW: 34W A19, 35W PAR30

V6TCW, V6TCRW: 75W A19

Juno Compatible Housing: Lamp Wattage/Type

IC2, IC22, IC22R, IC23: 40W A19 TC2, TC2R: 75W A19

ICPL6/PL6 Series: 13W max. CFL

Eyeball

V3029-WH: White

Outer Diameter: 7-3/4"

VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICNW, V6ICRW: 65W BR30, 75W PAR30L V6TCW, V6TCRW: 75W PAR30/PAR30L, 65W BR30

Juno Compatible Housing: Lamp Wattage/Type IC22, IC22R, IC23, IC2, TC2, TC2R: 75W PAR30

w/socket extender, 75W PAR30L, 65W BR30

**Drop Opal Lens Shower** with Reflector

V3041-PW: Plastic White

Outer Diameter: 8"

VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICNW, V6ICRW: 40W A19

Juno Compatible Housing: Lamp Wattage/Type

TC2, TC2R: 100W A19

ICPL6/PL6 Series: 26W max. CFL

Stippled Opal Lens Shower

V3020-PW: Plastic White

Outer Diameter: 8"

VuLite Housing: Lamp Wattage/Type

V6TCW, V6TCRW: 40W A19, 75W PAR30/PAR30L, 65W BR30,

75W PAR38

(Not for use with V6IC/V6ICR)

Juno Compatible Housing: Lamp Wattage/Type

TC2, TC2R: 60W A19, 75W PAR30/PAR30L, 65W BR30,

75W PAR38

Open Frame

V3050-WH: White

Aperture: 3-7/8"

Outer Diameter: 8"

VuLite Housing: Lamp Wattage/Type

V6ICW, V6ICRW, V6TCW, V6TCRW: 65W BR30

V6TCW, V6TCRW: 100W A19 IC22, IC22R, IC23: 40W A19 IC2: 60W A19













Cat. No.	Description	UPC Code	Pkg.	Wt.
V4ICW	4" Line Voltage IC New Construction Housing	66120927205	6	18
V4ICLVW	4" Low Voltage IC New Construction Housing	66120927206	4	36
V4TCW	4" Line Voltage TC New Construction Housing	66120927201	6	17
V4TCLVW	4" Low Voltage TC New Construction Housing	66120927203	6	30
V4TCRW	4" Line Voltage TC Remodel Housing	66120927202	6	10
V4TCRLVW	4" Low Voltage TC Remodel Housing	66120927204	6	20
V5ICW	5" Line Voltage IC New Construction Housing	66120927083	6	19
V5ICRW	5" Line Voltage IC Remodel Housing	66120927085	6	12
V5TCW	5" Line Voltage TC New Construction Housing	66120927084	6	24
V5TCRW	5" Line Voltage TC Remodel Housing	66120927086	6	17
V6ICW	6" Line Voltage IC New Construction Housing	66120925734	6	19
V6ICNW	6" Line Voltage IC New Construction Housing with Floating Socket	66120936353	6	19
V6ICRW	6" Line Voltage IC Remodel Housing	66120927198	6	12
V6TCW	6" Line Voltage TC New Construction Housing	66120927199	6	24
V6TCRW	6" Line Voltage TC Remodel Housing	66120927200	6	17
V2010-WH	5" Flat Lens Shower with Reflector	66120910749	12	8
V2015B-WH	5" Black Baffle	66120908085	12	4
V2015W-WH	5" White Baffle	66120908084	12	4
V2016C-WH	5" Clear Cone	66120908086	12	3
V2016W-WH	5" White Cone	66120908087	12	3
V2029-WH	5" R/PAR20 Eyeball	66120910754	12	12
V2030-WH	5" PAR30 Eyeball	66120927168	12	10
V3020-PW	6" Stippled Opal Lens Shower	66120910751	12	8
V3024B-WH	6" Conical Black Baffle	66120901731	48	18
V3024W-WH	6" Conical White Baffle	66120901730	48	18
V3025B-WH	6" Straight Black Baffle	66120907211	48	18
V3025W-WH	6" Straight White Baffle	66120907212	48	18



V3027C-WH	6" Clear Cone	66120910752	12	7
Cat. No.	Description	UPC Code	Pkg.	Wt.
V3029-WH	6" Eyeball	66120903872	12	15
V3034B-WH	6" Full Black Baffle	66120904472	48	24
V3034TB-WH	6" Full Black Baffle with Torsion Springs	66120901575	24	12
V3034TW-WH	6" Full White Baffle with Torsion Springs	66120901835	24	12
V3034W-WH	6" Full White Baffle	66120904473	48	24
V3037TW-WH	6" Full White Cone with Torsion Springs	66120902068	24	12
V3037W-WH	6" Full White Cone	66120904474	48	24
V3040N-PW	6" Stippled Opal Lens Shower w/Reflector	66120931746	12	18
V3041-PW	6" Drop Opal Shower	66120903864	12	20
V3050-WH	6" Open Frame	66120921084	24	13
V4010-BN	4" Line Voltage Brushed Nickel Gimbal Ring	66120927273	12	7
V4010-WH	4" Line Voltage White Gimbal Ring	66120921075	12	7
V4012-WH	4" Line Voltage Stippled Opal Lens Shower w/Reflector	66120910741	12	6
V4017C-WH	4" Line Voltage Clear Cone	66120921072	12	5
V4018-WH	4" Line Voltage Eyeball	66120910744	12	10
V4034B-WH	4" Line Voltage Black Baffle	66120921074	24	9
V4034W-WH	4" Line Voltage White Baffle	66120921073	24	9
V4040-BN	4" Low Voltage Brushed Nickel Gimbal Ring	66120927274	12	7
V4040-WH	4" Low Voltage White Gimbal Ring	66120921079	12	7
V4041-WH	4" Low Voltage Stippled Opal Lens Shower	66120912020	12	8
V4044B-WH	4" Low Voltage Black Baffle w/Regressed Gimbal Ring	66120910745	12	6
V4044W-WH	4" Low Voltage White Baffle w/Regressed Gimbal Ring	66120910746	12	6
V4047C-WH	4" Low Voltage Clear Cone w/Regressed Gimbal Ring	66120921078	12	6
V4048-WH	4" Low Voltage Eyeball with Baffle	66120910747	12	8



1300 South Wolf Road • Des Plaines, Illinois 60018 PHONE (847) 827-9880 • FAX (847) 827-2925 • junolightinggroup.com Regional Offices & Warehouses:

California, Georgia, Illinois, Indiana, Pennsylvania, Texas, Ontario CN





Products shown in this brochure are covered by U.S. and international patents and patents pending.
Specifications subject to change without notice.
© 2011 JUNO LIGHTING, LLC.